

DisplayPort Cables

Support for bandwidth of up to 10.8 Gbps, and providing superior performance than either HDMI or DVI



DisplayPort (with Latches)

Length(ft)	Male to Male	Male to Female
6	DISPLPORT6L	DPEXT6L
10	DISPLPORT10L	
15	DISPLPORT15L	
25	DISPLPORT25L	
35	DISPLPORT35L	
50	DISPLPORT50L	

Mini Displayport

Length(ft)	MiniDP - MiniDP	MiniDP-DP
3	MDISPLPORT3	
6	MDISPLPORT6	MPD2DPMM6

Panel Mount

Length(ft)	Part #
3	DPPNLFM3

Conxit Connection Wizard

StarTech.com's new ConXit Connection Wizard helps you find the right converter, extender, splitter, interface card or cable in two easy steps!



Visit: www.startech.com/conxit

For more products & detailed information visit www.startech.com/cables



1-800-265-1844



sales@startech.com

LIVE
CHAT

www.startech.com

StarTech.com

Hard-to-find made easy

Convert and scale VGA, DVI-D, DVI-I, Component, S-Video, Composite video formats



VGA Converters

Part #	Source (Input)	Input Audio Support	Display (Output)	Output Audio Support	Scaler
VGAHD2HDMI	VGA	Analog RCA	HDMI / DVI-D	HDMI	
VGA2HDMIPRO	VGA	3.5mm, SPDIF	HDMI / DVI-D	HDMI, SPDIF, 3.5mm	•
VGA2TV2WAY2	VGA (RGB / YPbPr)		VGA (RGB / YPbPr)		•
VGA2VID	VGA		Composite, S-Video		
VGA2NTSCPRO	VGA		Composite, S-Video		
VGA2DVII	VGA		DVI-I		•
VGA2CPNT	VGA		Component (YPbPr)		

DVI / HDMI Converters

Part #	Source (Input)	Input Audio Support	Display (Output)	Output Audio Support	Scaler
DVI2VGA	DVI-I		VGA (RGB / YPbPr)		•
DVI2VGACON	DVI-D		VGA		
DVI2HDMI	DVI-D	SPDIF (RCA)	HDMI	HDMI	
DVI2DVI	DVI-D		DVI-I		•
HDMI2DVI	HDMI	HDMI	DVI-D	SPDIF (RCA)	
HDMI2HDMI	HDMI / DVI	HDMI, SPDIF, 3.5mm	HDMI / DVI	HDMI, 3.5mm, SPDIF	•

Composite / S-Video / Component Video Converters

Part #	Source (Input)	Input Audio Support	Display (Output)	Output Audio Support	Scaler
COMP2VGA	Composite, S-Video		VGA		
VID2VGATV	Composite, S-Video		VGA (RGB / YPbPr)		•
VID2HDMITV	Composite, S-Video		HDMI / DVI		•
VID2VIDTV	Composite, S-Video				•
CPNT2VGAA	Component (YPbPr)	Analog RCA	VGA	3.5mm	
CPNT2DVI	Component (YPbPr)		DVI (RGB / YPbPr)		
CPNTTOS2HDMI	Component (YPbPr)	SPDIF	HDMI	HDMI	
CPNTA2HDMI	Component (YPbPr)	SPDIF (RCA)	HDMI	HDMI	

For more products & detailed information visit www.startech.com/av



1-800-265-1844



sales@startech.com

LIVE
CHAT

www.startech.com

StarTech.com

Hard-to-find made easy

USB and IP Video Adapters

Easily extend your desktop across multiple monitors. It's just like having an external video card for your desktop computer, laptop or netbook!

After installing the drivers, simply connect the external video adapter to your computer through the USB 2.0 port then connect your monitor to the video out port on the adapter. That's it... now you're ready to multi-task!



Multi-Monitor Display Adapters

Part #	Source	Display	Entry	Mid	Pro	Cable Form	Windows Aero	MAC	Audio
USB2VGAE2	USB (PC)	VGA	•						
USB2VGA	USB (PC)	VGA	•						
USB2VGA2	USB (PC)	VGA		•					
USB2VGAMM6	USB (PC)	VGA			•	•	•	•	
USB2VGAPRO	USB (PC)	VGA			•		•	•	
USB2VGADVI	USB (PC)	VGA & DVI-I		•					
USB2DVIE	USB (PC)	DVI-I	•						
USB2DVIE2	USB (PC)	DVI-I	•						
USB2DVI	USB (PC)	DVI-I		•			•	•	
USB2DVIMM6	USB (PC)	DVI-I			•	•	•	•	
USB2DVIPRO	USB (PC)	DVI-I			•		•	•	
IP2DVI	Ethernet	DVI-D							
IPUSB2HDMI*	Ethernet or USB	HDMI / DVI					•	•	USB Only

**Supports Mac® and Audio in USB mode only*

USB Video Capture Cables

Part #	Source	Display	Entry	Mid	Pro	Audio
SVID2USB2NS	S-Video, Composite	USB (PC)	•			
SVID2USB2	S-Video, Composite	USB (PC)		•		•
SVID2USB22*	S-Video, Composite	USB (PC)			•	•

**Features TWAIN Support*

For more products & detailed information visit www.startech.com/av



1-800-265-1844



sales@startech.com

www.startech.com

CONVERGEAV

Save Yourself Time and Money with Our Wide Range of Extenders

Our line of VGA video extenders use Cat 5/5e cabling to allow for longer distances and simple installation. StarTech.com offers signal management hardware and cabling for video extension and digital signage applications



Extenders

Part #	Signal Type	Receiver Included	Series/Family	Ports	Audio	Mountable	Wall-Plate	Passive	Active	Distance*
ST121UTP	VGA	•	ST121			•			•	500ft
ST122UTPA	VGA	•	ST121		•	•			•	500ft
ST121EXT	VGA		ST121			•			•	500ft
ST1214T	VGA		ST121	4					•	500ft
ST1218T	VGA		ST121	8					•	500ft
ST121R	VGA		ST121			•			•	500ft
ST121UTP232	VGA	•							•	950ft
ST121UTPDVI	DVI	•							•	150ft
ST121HDMIT	HDMI				•				•	150ft
ST121HDMR50	HDMI				•				•	150ft
SVIDUTPEXT	S-Video	•						•		600ft
SVIDUTPEXTA	S-Video	•			•	•		•		600ft
COMPUTPEXTA	Composite	•			•	•		•		600ft
COMPUTPWALLA	Composite	•			•		•	•		600ft
CPNTUTPEXT	Component	•						•		600ft
CPNTUTPWALLA	Component	•			•		•	•		300ft

*Distance varies by resolution, see website for more details

For more products & detailed information visit www.startech.com/av



1-800-265-1844



sales@startech.com

LIVE
CHAT

www.startech.com

StarTech.com

Hard-to-find made easy

CONVERGEAV

UTPE/UTPEA Series VGA Extenders

The UTPE/UTPEA Series offers point to multi-point 4 and 8 port extenders with the option of using a repeater / line splitter to run up to 32 displays. Plus, our wall plate extenders work with the existing UTPE/UTPEA series for a cleaner and more professional installation



VGA over Cat5 Extenders

Part #	Transmitter	Receiver	Series/ Family	Ports	Audio	Mountable	Wall-Plate	Active	Distance
ST121UTPEP	•	•	UTPE					•	250ft
ST124UTPE	•		UTPE	4				•	950ft
ST128UTPE	•		UTPE	8				•	950ft
STUTPRXL		•	UTPE			•		•	950ft
STUTPTXWAL	•		UTPE				•	•	950ft
STUTPRXWAL		•	UTPE				•	•	950ft
STUTPWALL	•	•	UTPE				•	•	950ft
ST124UTPEA	•		UTPEA	4	•			•	950ft
ST128UTPEA	•		UTPEA	8	•			•	950ft
STUTPEALR		•	UTPEA		•			•	950ft
STUTPEA4X			UTPEA	4	•			•	950ft
STUTPTXWLA	•		UTPEA		•		•	•	950ft
STUTPRXWLA		•	UTPEA		•		•	•	950ft
STUTPWALLA	•	•	UTPEA		•		•	•	950ft

**Distance varies by resolution, see website for more details*

For more products & detailed information visit www.startech.com/av



1-800-265-1844


sales@startech.com
www.startech.com

CONVERGEAV**The Right Video Splitter to Meet the Demanding Needs of any Application**

Split/distribute VGA, DVI, Composite, Component, and HDMI signals for optimum video distribution

**Splitters****Performance Level**

Part #	Signal Type	Ports	Entry	Mid	Pro	Audio	Mountable	1080p	HDCP
ST122LE*	VGA	2		•					
ST122W	VGA	2	•				•		
ST122L	VGA	2		•				•	
ST122PRO	VGA	2			•			•	
ST122PROA	VGA	2			•	•		•	
ST122HDMI	HDMI	2			•	•		•	•
ST123HDA	Component	3			•	•		•	
ST124W	VGA	4	•				•		
ST124L	VGA	4		•				•	
ST124PRO	VGA	4			•			•	
ST124HDMI	HDMI	4			•	•		•	•
ST128W	VGA	8	•				•		
ST128L	VGA	8		•				•	
ST128PRO	VGA	8			•			•	
ST128HDMI	Component	8			•	•	•	•	•
ST128CPNTA	Component	8			•	•	•	•	
ST1216PRO	VGA	16			•			•	

*USB powered, no power adapter required

For more products & detailed information visit www.startech.com/av



1-800-265-1844



sales@startech.com

LIVE
CHAT

www.startech.com

StarTech.com

Hard-to-find made easy

Professional Rack-mountable and Home Theater Switches for Component, VGA, DVI, and HDMI Connectivity

Maximize video output capability using a multiple video sources to toggle on one display



Switchers

Part #	Signal Type	Ports	Infrared	RS-232	Audio	Matrix	Mountable	1080p	HDCP
ST122VGAU	VGA	2						•	
VS415RVGA	VGA	4	•					•	
VS815RVGA	VGA	8	•					•	
VS410RVGAA	VGA	4	•	•	•		•	•	
CPNT410IR	Component	4	•		•			•	
VS421CPNTA	Component	4	•	•	•		•	•	
VS410HDMIE	HDMI	4	•		•			•	•
VS310HD2HDMI	VGA/Component/HDMI	1	•		•				
ST222MX	VGA	2 x 2				•		•	
ST224MX	VGA	2 x 4				•		•	
ST228MX	VGA	2 x 8				•		•	
ST424MX	VGA	4 x 4	•		•	•	•	•	
VS420RDVIA	DVI	2 x 4	•		•	•	•		

Conxit Connection Wizard

StarTech.com's new ConXit Connection Wizard helps you find the right converter, extender, splitter, interface card or cable in two easy steps!

Visit: www.startech.com/conxit



For more products & detailed information visit www.startech.com/av



1-800-265-1844



sales@startech.com

www.startech.com