

Desktop KVM

VGA, DVI, HDMI, and DisplayPort KVMs

A huge selection of KVMs including unique multi-monitor versions for demanding multimedia applications.



2 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub SV231DD2DUA

MULTI-MONITOR KVMs

| # of Ports | Input Interface | Video | Audio | Part Number |
|------------|-----------------|-------------------------------------|-------|-------------------------|
| 2, 4 Ports | PS/2 | VGA + VGA, Dual Monitor | No | SV221DD/SV421DD |
| 2, 4 Ports | USB | DVI + DVI, Dual Monitor | Yes | SV231DD2DUA/SV431DD2DUA |
| 2, 4 Ports | USB | VGA + DVI, Dual Monitor | Yes | SV231DDVDUA/SV431DDVDUA |
| 2 Ports | USB | DVI + DVI + DVI + DVI, Quad Monitor | Yes | SV231QDVIUA |


USB KVMs

| # of Ports | Input Interface | Video | Audio | Features | Part Number |
|------------|-----------------|---------------|-------|-------------------------------|---------------------------|
| 2 Ports | USB | VGA | Yes | Ultra compact on a cable | SV215MICUSBA |
| 2 Ports | USB | DVI | Yes | Ultra compact on a cable | SV215MICDVI |
| 2 Port | USB | VGA | Yes | Kit with cables | SV211KUSB |
| 2, 4 Ports | USB | DVI | Yes | Kit with cables | SV211KDVI/SV411KDVI |
| 2, 4 Ports | USB | VGA | No | Professional Series | SV231USBGB/SV431USB |
| 4 Ports | USB | VGA | Yes | Professional Series | SV431USBAGB |
| 2, 4 Ports | USB | VGA | Yes | Built-in Ethernet Network Hub | SV231USBANGB/SV431USBANGB |
| 2, 4 Ports | USB | DVI | Yes | Built-in USB 2.0 hub | SV431UADVIGB |
| 2, 4 Ports | USB | DVI Dual-Link | Yes | High resolution 2560x1600 | SV231DVIUAHR/SV431DVIUAHR |



4 Port High Resolution DVI Dual Link KVM Switch with Audio SV431DVIUAHR

Ideal for switching between a PC and Notebook



DISPLAYPORT KVMs

| Description | Part Number |
|---|-------------|
| 2 Port DisplayPort KVM (Digital Audio only) | SV231DPU |
| 2 Port DisplayPort KVM (Digital & Analogue Audio) | SV231DPUA |
| 4 Port DisplayPort KVM (Digital & Analogue Audio) | SV431DPUA |

PS/2 KVMs

| # of Ports | Input Interface | Video | Features | Part Number |
|------------|-----------------|-------|--------------------------|----------------|
| 2 Ports | PS/2 | VGA | Ultra compact on a cable | SV221MICRO |
| 2 Ports | PS/2 | VGA | Kit with cables | SV211K |
| 2, 4 Ports | PS/2 | DVI | Professional Series | SV221DVI |
| 2, 4 Ports | PS/2 | VGA | Professional Series | SV231/SV431HGB |

UNIVERSAL KVM CABLES

| Length | KVM Connectors | PC Connectors | Part Number |
|-------------------------|------------------|------------------|-------------|
| 6, 10, 15ft | USB+VGA | USB+VGA | SVUSB2N1_x |
| 6, 15ft | USB+DVI+SPKR+MIC | USB+DVI+SPKR+MIC | USBDVI4N1Ax |
| 6, 10, 15ft | DB15 | USB+VGA | SVECONUSx |
| 6, 10, 15, 25, 50ft | DB15 | PS/2+VGA | SVECONx |
| 6, 10, 15, 25, 35, 50ft | PS/2+VGA | PS/2+VGA | SVPS23N1_x |
| 6, 10, 15, 25, 50ft | PS/2+VGA | PS/2+VGA | PS23N1THINx |

x = Length

For additional KVMs, dongles, accessories, and a large selection of KVM cables of varying lengths, please visit our website at www.startech.com/kvm

QUESTIONS?
PHONE
 00-800-7827-8324
LIVE CHAT
www.startech.com



StarTech.com
 Hard-to-find made easy®

Enterprise KVM & LCD Consoles

Server Room Solutions

Solutions for taking full control of the server room, including local, long distance, and full remote over IP.



Rackmount, IP, and Matrix KVMs

A full line of LCD Consoles and versatile enterprise level KVM switches, from standard cabled rackmount models to multi-user matrix IP KVMs.



4 Port USB VGA IP KVM Switch with Virtual Media SV441DUSBI

Control multiple servers or KVMs remotely. Supporting VGA and USB, as well as virtual media means not only can you control your machines remotely, but have full access for remote software or operating system installations.

RACKMOUNT KVM

| # of Ports | Extra Features | Part Number |
|------------|----------------|--------------|
| 8 Ports | RackMount | SV831DUSBGB |
| 8 Ports | Audio Support | SV831DUSBAU |
| 16 Ports | RackMount | SV1631DUSBGB |



1 Port IP KVM with Virtual Media SV1107IPEXT

IP KVMs

| # of Ports | Simultaneous Users | Extra Features | Part Number |
|--------------|--------------------|---------------------------------------|--------------------------|
| 1 Port | 1 | Virtual Media | SV1107IPEXGB |
| 1 Port | 1 | Virtual Media Plus Serial, USB & PS/2 | SV1115IPEXGB |
| 8, 16 Ports | 1 | RackMount | SV841HDIEGB/SV1641HDIEGB |
| 16, 32 Ports | 3 (Matrix) | Virtual Media, Serial, USB & PS/2 | SV1653DXI/SV3253DXI |
| 16, 32 Ports | 4 (Matrix) | Virtual Media, Serial, USB & PS/2 | SV1654DX4I/SV3254DX4I |

LCD, KVM and IP KVM Consoles

A full range of LCD sizes from 15in to an industry leading 20in, with connectivity for VGA & DVI, and configurations from 1 to 16 ports.

LCD CONSOLES - PROFESSIONAL SERIES

| # of Ports | Size | Part Number |
|------------|------|--------------|
| 1 Port | 17in | RKCONS1701GB |
| 1 Port | 19in | RKCONS1901GB |
| 8 Ports | 17in | RKCONS1708GB |
| 16 Ports | 17in | RKCONS1716GB |
| 16 Ports | 19in | RKCONS1916GB |



1U 20in High Resolution Folding Rack Mount LCD Console for 19in Rack RKCONS2001GB

For maximum control and usability, the RKCONS2001GB supports both DVI and VGA servers and KVMs, and boasts the largest screen size (20.1in), and highest resolution (1600x1200) screen available in a rack mountable LCD Console.

LCD CONSOLE WITH BUILT-IN CONTROL OVER IP

| # of Ports | Size | Part Number |
|------------|------|--------------|
| 16 Port | 17in | CBCON1716IGB |



KVM Console to USB 2.0 Portable Laptop Crash Cart Adapter NOTECONS01

With the NOTECONS01, your laptop quickly becomes a portable console allowing you to connect to and control any PC or headless server with a VGA and USB port.

In the News

"StarTech.com's USB KVM may be your new best friend for trips to the datacentre... you can use this from the back of the rack. So if you are handling issues that require moving cables or network connections this can be a major timesaver!" - everythingUSB.com

QUESTIONS?

PHONE

00-800-7827-8324

LIVE CHAT

www.startech.com



StarTech.com
Hard-to-find made easy®