


Note:
1. Support Resolution:3840*2160P/60Hz

5	Key Ring\Stainless Steel\Nickel Plating\φ25.2*T2.5mm	1Pcs
4	Screw Nickel plating SIZE:PB φ2*L4*D3.5mm	4Pcs
3	Black plastic bracket\L18.9*W12.8*H6.25mm	1Pcs
	Bottom Shell,Color Black\USB-C to MINI DP\L48*W32*H7mm\Spraying rubber oil	1Pcs
2	TOP Shell,Color Black\USB-C to MINI DP\L48*W32*H8mm\Spraying rubber oil	1Pcs
	TYPE-C TO MINI DP\Connector nickel plating	1Pcs
1	CABLE USB-C , Type-C\M+FPC, COLRO:BLACK	1Pcs
NO	DESCRIPTION	Q' ty

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	CDP2DPFC		
DESCRIPTION	USB-C TO DP ADAPTER WITH FLEX CABLE & RETAINER		
REV: A	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 03/16/2020