


# DisplayPort 1.4 Active Optical Cable - M/M

DP14MMxxMAO



Wire Pin Assignment and Wire Description:

CN1.	Signal Assignment	CN2.	WIRE
1	ML_Lane0 (p)	1	OP4
2	GND	2	N/A
3	ML_Lane0 (n)	3	OP4
4	ML_Lane1 (p)	4	OP3
5	GND	5	N/A
6	ML_Lane1 (n)	6	OP3
7	ML_Lane2 (p)	7	OP2
8	GND	8	N/A
9	ML_Lane2 (n)	9	OP2
10	ML_Lane3 (p)	10	OP1
11	GND	11	N/A
12	ML_Lane3 (n)	12	OP1
13	GND	13	N/A
14	GND	14	N/A
15	AUX_CH (p)	15	#28
16	GND	16	#32
17	AUX_CH (n)	17	#28
18	Hot Plug	18	#28
19	DP_PWR Return	19	#26
20	DP_PWR	20	N/A

LENGTH TABLE:

SKU	LENGTH
DP14MM10MAO	10.0 <sup>+0.4</sup> <sub>0</sub> M
DP14MM15MAO	15.0 <sup>+0.4</sup> <sub>0</sub> M

ITEM	CTI P/N	DESCRIPTION	QTY
7	AZDA005	LABEL W40mm*L30mm	1
6	AZCD026	SR PVC 45P	1
5	AZCF028	Bottom Shell PC	2
4	AZCF030	Top Shell ("Display End") PC	1
3	AZCF027	Top Shell PC	1
2	AZCF029	DP plug, front metal shell	2
1	1S8204	HYBRID HDMI CABLE Black	1