

Rocking Under-Desk Footrest - Cable Management

Product Diagram (FTRST2)



Part	Function
1 Footrest Platform	• Rest feet on the Footrest Platform
2 Cable Management Storage Space	• Store a Single Strip UL-Certified Power Bar • Feed Cables out of cutouts in the back and sides
3 Base	• Curved design to allow for a back and forth movement

Warnings

- Always use dry footwear.
- Always store wet footwear and open containers of liquid away from the **Rocking Under-Desk Footrest**.
- Do not stand on the **Rocking Under-Desk Footrest**.

Requirements

For the latest requirements please visit: www.startech.com/FTRST2.

- (Optional) Single Strip UL-Certified Power Bar x 1

(Optional) Installation

1. Ensure the **Single Strip UL-Certified Power Bar** is powered **Off**.
2. Access the **Cable Management Storage Space** by unfolding the **Footrest Platform** from the **Base**.
3. Apply the **20 x 40 mm Tape** to one side of the **Single Strip UL-Certified Power Bar**.
4. Press the taped side of the **Single Strip UL-Certified Power Bar** into the **Cable Management Storage Space** with the **Outlets** pointed towards the front and the **Cable** from the **Single Strip UL-Certified Power Bar** routed out of the side.
5. Route the **Cables** through the gap at the front and into the **Single Strip UL-Certified Power Bar** and plug the **Cables** into the **Outlets**. (Figure 1)

Figure 1



6. Power **On** the **Single Strip UL-Certified Power Bar**.
7. Fold the **Footrest Platform** over the **Base**.

Note: Exercise caution when folding to avoid damaging the **Cables**.

8. Place the **Rocking Under-Desk Footrest** under the **Desk**.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Warranty Information

This product is backed by a five-year warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

StarTech.com Ltd.	StarTech.com LLP	StarTech.com Ltd.	FR: fr.startech.com
45 Artisans Cres	2500 Creekside	Unit B, Pinnacle 15	DE: de.startech.com
London, Ontario	Parkwy	Gowerton Rd,	ES: es.startech.com
N5V 5E9	Lockbourne, Ohio	Brackmills	NL: nl.startech.com
Canada	43137	Northampton	IT: it.startech.com
	U.S.A.	NN4 7BW	JP: jp.startech.com
		United Kingdom	