

8-Port Rack-Mount PDU with C13 Outlets - 1U - 16 A


PDU08C13H

- FR: Guide de l'utilisateur - fr.startech.com
- DE: Bedienungsanleitung - de.startech.com
- ES: Guía del usuario - es.startech.com
- NL: Gebruiksaanwijzing - nl.startech.com
- PT: Guia do usuário - pt.startech.com
- IT: Guida per l'uso - it.startech.com

Introduction

The PDU08C13H is a cost-effective power distribution solution that you can mount in your rack to deliver power to your rack-mounted equipment. The PDU is constructed from durable steel and mounts horizontally in your rack, taking up only 1U of space. The PDU features a dual circuit breaker that is designed to protect your equipment from power surges, and two reset buttons that you can use to reset the PDU after a power surge.

Product diagram



*actual product may vary from photos

Package contents

- 1 x rack-mount PDU
- 1 x 10 ft. (3 m) C19 to NEMA5-20p power cord
- 4 x screws
- 4 x cage nuts
- 1 x instruction manual

Requirements

- Power source
- 1U of space in a server rack

Requirements are subject to change. For the latest requirements, please visit www.StarTech.com/PDU08C13H.

Installation

The rack-mount PDU takes up 1U of space.

1. Line up the **Mounting holes** on the rack-mount PDU with the mounting holes on your server rack.
2. Use the provided screws and cage nuts or the mounting hardware that came with your rack to attach the rack-mount PDU to your server rack.
3. Connect the power cord to the **C20 power port** on the rack-mount PDU and a power source. Make sure that you connect the power cord directly to the power source and not another PDU.
4. Connect the devices in your server rack to the **C13 outlets** on the rack-mount PDU.

Caution! The combined power draw of all of the devices attached to the rack-mount PDU shouldn't exceed 16 A, otherwise you will trip the built-in circuit breaker.

Troubleshooting

What do I do if I trip the circuit breaker?


If you trip the circuit breaker, complete the following:

1. Make sure that the combined power draw of all of the devices attached to the rack-mount PDU doesn't exceed 16 A.
2. Press one of the **Reset buttons** on the rack-mount PDU.

Specifications

Input	C20
Output	C13 (x8)
Voltage	100 to 240 V ac
Maximum current	16 A
Number of fuses	2

M5 Screws Assembly Instructions





Points de collecte sur www.quefairede mesdechets.fr
Privilégiez la réparation ou le don de votre appareil !

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two-year warranty.

StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.