



6.3+0.2/-0mm



- REMARKS:
- 1.PLUG(SF-81) RATED POWER:125V 10A
 - 2.CONNECTOR(SF-82S)RATED POWER:125V 10A
 - 3.WIRE:SVT 3X18AWG 60°C RATED VOLTAGE:300V
 - 4.DVW TEST:1500VAC,1S
 - 5.POLARIZATION AND CONTINUITY TEST
 - 6.COLOR:BLACK
 - 7.COMPLY WITH UL817 STANDARD

THIRD ANGLE PROJECTION



Conductor		Insulation (PVC 60°)			Jacket (PVC 60°)		Overall diameter
mm ²	Resistance max	Min.Thick	Diameter	Length of Lay	Min.Thick	AVG.Thick	
41/0.154	at 20°C ≤22.4ohms/km	0.342mm	2.3±0.05mm	44 ↓mm	0.61mm	0.76mm	

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

PRODUCT ID	PXT1001		
DESCRIPTION	1 ft Standard Computer Power Cord Extension - C14 to C13		
REV: A	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 04/29/2020