



CDP2HDM5MH	5000+120/-0mm
CDP2HDM4MH	4000+100/-0mm
CDP2HDM3MH	3000+80/-0mm
Part Number	Length(L±M)

NO	DESCRIPTION	Q'ty
5	LDPE-PE101	4.70g
4	60P PVC BLACK	4.50g
3	USB-C to HDMI M Shell,Color Black	1 Pcs
	USB-C to HDMI M Front Cover,Color Black	1 Pcs
2	PCBA\USB-C TO HDMI A/M \IC:RTD2172U,Connector Nickel plated	1 Pcs
2	USB-C/M,smooth Black shell	1 Pcs
1	USB-C\I to USB-C\I Cable,Connector Nickel plated Cable\OD:4.8mm\UL2725 [30AWG(1\0.254T)*2C+D+AL+HM] *4P+32AWG*1P+34AWG*4C+ 24AWG*2C+F+D+AB,JACKET PVC BLACK(No Vendor Logo)	0.5Pcs

THIRD ANGLE PROJECTION

GENERAL NOTES
DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	CDP2HDM3MH, CDP2HDM4MH, CDP2HDM5MH
DESCRIPTION	USB C to HDMI Cable 4K 60Hz w/ HDR10 - Ultra HD USB Type-C to 4K HDMI 2.0b Video Adapter Cable - USB-C to HDMI HDR Monitor/Display Converter - DP 1.4 Alt Mode HBR3
DO NOT SCALE	SHEET: 1 OF: 1
UPLOAD DATE:	9/20/2021