

## 12U 19in Hinged Wall Mount Server Rack Cabinet with Mesh Door

RK1219WALHM

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

### Packaging Contents

- 1 x RK1219WALHM cabinet
- 1 x Package of cabinet screws and cage nuts
- 1 x Set of keys

Prior to mounting the cabinet to a wall, ensure the 4 wall mounting screws (not included) are properly installed into sturdy structures and will be able to support the weight of the cabinet, plus any accessories that will be installed.

To attach the RK1219WALHM to a wall, fasten the back of the unit onto 4 evenly distributed wall mounting screws.

With two removable side panels, RK1219WALHM provides access from any side, once attached to the wall. A rear-panel hinge provides easy access by swinging the whole cabinet open, while a front wire mesh door provides a view of internal items.



\*actual product may vary from photos

### Specifications

<b>Description</b>	DuraRak 12U 19" Black Hinged Wall Mount Server Rack Cabinet with Steel Mesh Door
<b>Material</b>	SPCC
<b>Colour</b>	Black
<b>Mounting Depth</b>	16.25 in (max)
<b>Weight Capacity</b>	60 kg (130 lbs)
<b>Dimensions</b>	550.0 mm x 600.0 mm x 635.0 mm (DxWxH)
<b>Net Weight</b>	29.5 kg (65.2 lbs)
<b>Standards</b>	EIA RS310-C

## **Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols**

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

## **Technical Support**

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit [www.startech.com/downloads](http://www.startech.com/downloads)

## **Warranty Information**

This product is backed by a lifetime year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

## **Limitation of Liability**

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.