


Part Number	Length (x)	Color(y)
RUSB2CC1MB	1000±30	BLACK
RUSB2CC2MB	2000±30	BLACK
RUSB2CC1MW	1000±30	WHITE
RUSB2CC2MW	2000±30	WHITE

(A). Wire Pin Assignment and Wire Description:

CN.1	Signal Name	CN.2	COLOR
A4,B4,A9,B9	PWR_Vbus1	A4,B4,A9,B9	RED
A5	CC	A5	BLUE
A7	UTP_Dn	A7	WHITE
A6	UTP_Dp	A6	GREEN
A1,B1,A12,B12	GND_PWRrt1	A1,B1,A12,B12	DRAIN
SHORT	SHELL	SHORT	BRAID




(B). Electrical Testing :

- Open/Short:100%. Testing Line-Process.
- HI-POT: 100V AC/0.1sec.
- Insulation Resistance: 10MΩ (MIN) 100V DC

ITEM	MATERIALS LIST & SPEC. DESCRIPTION	Q'TY
③	MOLDED TPE COLOR(C)	/
②	USB 2.0 TYPE C MALE, (TERMINAL:GOLD PLATED, SHELL:NI-PLATED)	2PCS
①	USB 2.0 [32AWGx2C+22AWGx1C+32AWGx1C+2E]+AB OD:3.1mm JACKET TPE COLOR(C)	/

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE  
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	RUSB2CCxMy
DESCRIPTION	Durable Fast Charge & Sync USB 2.0 Type C to USB C Laptop Charger Cord TPE Jacket Aramid Fiber M/M 60W
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 5/12/2021