

USB 3.0 Capture Device for VGA Video

Product ID (USB32VGCAPRO)

Product Diagram

Front View



**Product may vary from images*

Back View



**Product may vary from images*

Product Information & Requirements

For the latest drivers, software, manuals, product information, technical specifications, and declarations of conformance, please visit:

www.StarTech.com/USB32VGCAPRO

- VGA video source with cabling x 1
- VGA display with cabling (optional for video passthrough) x 1

Package Contents

- USB 3.0 capture device for VGA video x 1
- 3.3 ft [1 m] USB 3.0 cable x 1
- 3.3 ft [1 m] VGA cable x 1
- 6ft [2m] USB-C to USB-B Cable x 1
- Quick-Start Guide x 1

Installation

Driver Installation

Navigate to www.StarTech.com/USB32VGCAPRO and select the **Drivers/Downloads** tab to locate and download the latest **Driver**.

Software Installation

Navigate to www.StarTech.com/USB32VGCAPRO and select the **Drivers/Downloads** tab to locate and download the latest **Windows Video Capture Software** and the accompanying **Software User Guide**.

Hardware installation

 To use the video adapter in USB mode, ensure the software installation steps have been completed **before you connect the adapter to your computer**.

1. Connect a VGA cable (sold separately) to the output port on your video source device and to the video adapter's **VGA In** port.
2. Connect the included USB cable to the video adapter's **USB** port, and to a USB port on your computer system.
3. Your computer will automatically detect the USB drivers for the video adapter and install them.
4. To preview the video source that's being sent through the capture device, by connecting a VGA cable (not included) to the video adapter's **VGA Out** port and to a VGA display.

Regulatory Compliance

FCC - Part 15

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation.

This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

(1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Changes or modifications not expressly approved by StarTech.com could void the user's authority to operate the equipment.

Industry Canada Statement

This Class B digital apparatus complies with Canadian ICES-003.

Cet appareil numérique de la classe [B] est conforme à la norme NMB-003 du Canada.

CAN ICES-3 (B)/NMB-3(B)

This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions:

(1) This device may not cause interference, and (2) This device must accept any interference, including interference that may cause undesired operation of the device.

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes:

(1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Warranty Information

This product is backed by a two-year warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

StarTech.com Ltd.

45 Artisans Crescent
London, Ontario
N5V 5E9
Canada

StarTech.com LLP

4490 South Hamilton
Road
Groveport, Ohio
43125
U.S.A.

StarTech.com Ltd.

Unit B, Pinnacle 15
Gowerton Road
Brackmills,
Northampton
NN4 7BW
United Kingdom

StarTech.com Ltd.

Siriusdreef 17-27
2132 WT Hoofddorp
The Netherlands

FR: startech.com/fr
DE: startech.com/de
ES: startech.com/es
NL: startech.com/nl
IT: startech.com/it
JP: startech.com/jp