

2017 ISSUE II

# CONNECTIVITY GUIDE

THE INSIDE EDGE ON CONNECTING  
TECHNOLOGY SOLUTIONS

  
Includes 3  
Product Finders

EXPERIENCE THE  
PERFORMANCE OF USB-C

CONNECT ANY DEVICE TO  
ANY DISPLAY

THUNDERBOLT 3: POWERFUL,  
PORTABLE, PRACTICAL

A FLEXIBLE WORKSTATION  
DESIGNED FOR COMFORT

MANAGE AND EXPAND  
YOUR NETWORK

MUST-HAVE ROAD  
WARRIOR TOOLS

THE MODERN WORKSTATION

MODERN MEETING ROOMS

THE PERFECT DOCK

## Message from Paul



Welcome to our latest Connectivity Guide, a publication designed to keep you informed on the latest connectivity related technologies, trends and products that are important to IT professionals.

The momentum for USB-C adoption continues to build. This new connector type is now standard on many brands of devices including HP, Dell, Lenovo and Apple who have dropped legacy ports in favour of the new USB Type-C ports in some of their models.

By the end of 2017 it is estimated that over 50% of new laptops will have USB Type-C ports built-in. As technology users will need to connect their USB-C laptops to devices with older connector types, the need for adapters, cables and converters to bridge the new and older standards will rise.

To ensure you can always make your USB-C connection, our Market Research and Product Development teams have been hard at work identifying and creating the products you will want before you need them. We now have over 100 USB-C products available with new ones launching every week.

In this guide, you'll learn about unique solutions to maximize productivity and efficiency in environments ranging from the boardroom to the back office. We also feature the exclusive "Presentation Adapter", a new StarTech.com product that will ensure your presentations will never be interrupted again.

All the best,

**Paul Seed**  
CEO/Co-Founder  
StarTech.com

StarTech.com helps you become an IT hero by making it easy to identify, find, get & use the connectivity parts you need. **Here's how:**

- Over 3000 products supporting 200 technologies**  
From legacy to latest, all the products you need to enable your solutions from one convenient source
- Time-saving tools & resources**  
The ConXit connection wizard, brand compatibility grids and other exclusive tools make your job easier
- 24 hour support**  
Access to FREE, pre and post sales support to ensure you get the information & products you need



Need help making your connection?

- Live Chat
- Email
- Phone

[www.startech.com/be/support](http://www.startech.com/be/support)

# What's Inside

- 4 The Modern Workstation
- 6 A Flexible Workstation Designed for Comfort
- 8 Connect Any Device to Any Display
- 10 The Perfect Dock
- 12 Manage and Expand Your Network
- 14 Thunderbolt 3
- 16 Experience the Performance of USB-C
- 18 Modern Meeting Rooms
- 20 Must-Have Road Warrior Tools
- 22 **Quick Finder Grids**  
USB-C & Thunderbolt 3  
Display Mounting  
Docking Stations

COVER STORY



# The Modern Workstation: Connectivity Meets Comfort

Our wide selection of docking stations, monitor mounts and charge hubs keep you connected and comfortable in any workspace configuration.



## Connect to a workstation

Use a single USB-C cable to connect your laptop to a dual-monitor workstation along with additional devices.



**USB-C Dual-Monitor Docking Station with Power Delivery.**  
MST30C2DPPD

Use the **Dual Monitor Mount** to create more work space with two monitors.



ARMDUAL

## Looking for a single or triple monitor option?



Set up a compact work space that doesn't leave you short on connections with this **4K DisplayPort Docking Station.**  
USB3VDOCK4DP

Use our space-saving **Cubicle Hanging Monitor Mount** for a single display.

ARMCBCL



Create a high-performance, ultra HD workstation with our **Triple Monitor Docking Station** which can support four displays, including one 4K DisplayPort.  
USB3DOCKH2DP

Try our **Triple Monitor Desk Mount** to maximize desk space and productivity.

ARMTRIO



## Power up

Use this **7-Port USB Hub** with 2 Fast Charge Ports to connect to the USB devices at your desk and fast charge your phone or tablet.  
ST93007U2C



2 Fast Charge Ports

## Work in comfort

Transition easily between sitting or standing and work more ergonomically with our **Sit-to-Stand Workstation.**  
ARMSTS



## Add a monitor

Keep a clean workstation and reduce costs by combining your cables and adapters. Use our video adapter cables to connect your device or docking station directly to a monitor.



MDP2DVIMM6BS

MINI DISPLAYPORT TO DVI

HDDVIMM2M

HDMI TO DVI

CDP2DPMM6B

DISPLAYPORT TO USB-C




# A Flexible Workstation Designed for Comfort

Our space-saving monitor mounts combine with our easy-adjustment sit-to-stand desks to make more comfortable and productive workstations.

This desk can support two monitor stands or arms, increasing overall productivity, comfort and employee health.

The large **Sit-to-Stand Workstation** is a cost-effective, adjustable and ergonomic solution for creating a more comfortable work area.

ARMSTSL

 Easy to integrate into a traditional cubicle



Easy access to multiple screens helps you analyze complex documents, create killer code, or edit content quickly.

Free up desk space, customize monitor position and create an impressive workspace with our **multiple monitor mounts**.

ARMQUAD   
 ARMTRIO   
 ARMDUAL30 



## Why ergonomic solutions matter

-  Musculoskeletal disorders & cases accounted for **33%** of all worker injury and illness cases<sup>1</sup>
-  Estimated direct cost of absenteeism in CA/US/UK was 16.6 billion in 2012<sup>2</sup>
-  For every 100 employees, MSDs cost employers about \$103,000 annually<sup>3</sup>



Premium Polyurethane

Reduce strain on your feet, knees, hips and back.

For added comfort and ergonomic support, add our new **Anti-Fatigue Mat**. The premium polyurethane offers a durable cushion to stand on.

STSMAT



This sturdy monitor mount gets your monitor off your desk.

Customize the position of your monitor with the **Desk-Mount Monitor Arm**.

ARMPIVOTHD

 Easy height adjustments  Heavy duty aluminium construction



Built-in Drawer

Raise your monitor up to eye-level with our new **Height Adjustable Monitor Riser**.

MONSTADJDL

# Connect Any Device to Any Display

From legacy technology to cutting edge connectivity, StarTech.com brings you the widest selection of display adapters. Connect easily to multiple monitors for increased productivity or plug-and-play to any projector to ensure your next presentation goes smoothly.

**NEW!** Introducing our new Presentation Adapter.

## We keep your computer awake. The audience is up to you.

Our Presentation Adapter features a unique Presentation Mode switch that keeps your laptop awake while connected to a projector. This adapter is the perfect accessory for boardrooms where long meetings may cause laptops to go into power-save mode.

When the switch is turned on, the laptop display will not enter sleep mode.

HDMI CDP2HD4K60SA  
VGA CDP2VGASA



- 1 Display your DisplayPort enabled device to a VGA projector or monitor. **DP2VGA2**
- 2 Connect your laptop to an HDMI projector or monitor through the Mini DisplayPort port on your laptop. **MDP2HDMI**
- 3 Extend your USB-C laptop's screen to a VGA projector or monitor. **CDP2VGA**



Switch  
⏴

Use adapter cables as a cost-effective and clutter-free way to connect your laptop or docking station directly to your monitor.

Mini DisplayPort to HDMI MDP2HDMM2MB  
DisplayPort to DVI DP2DVIMM10  
USB-C to DisplayPort CDP2DPMM6B



This sleek, **4-in-1 adapter** conveniently connects your USB-C computer to a VGA, DVI, HDMI®, or Mini DisplayPort display. **CDPVGDVHDMDP**

Multiple monitors instantly boost productivity.



Connect your Thunderbolt 3 MacBook or Windows laptop to two high-resolution 4K60 DisplayPort monitors with our **Thunderbolt 3 to Dual DisplayPort Adapter**. **TB32DP2T**



Maximize productivity with our **USB-C to DisplayPort Multi-Monitor Splitter** which allows you to connect your laptop to two monitors. **MSTCDP122DP**



Connect your computer to four displays and make multi-tasking easier with this **DisplayPort to DisplayPort Multi-Monitor Splitter**. **MSTDP124DP**

# The Perfect Dock

Whatever your needs, we have a docking station for you.

Your unique workstation requirements demand versatility. Our broad universal docking station selection makes it easy to find the best way to turn any laptop into the ideal workstation solution.



## Convenient, compatible connectivity



Create the ultimate high-performance workstation while charging your Thunderbolt 3 laptop. This **Thunderbolt™ 3 Dual-4K Docking Station** maximizes connectivity for your MacBook or Windows laptop.

TB3DK2DPPDU

4K Dual Monitors USB-C Power Delivery



Take being productive to another level with our unique **USB-C Triple Monitor Docking Station**, which offers the ability to connect to three monitors while powering your laptop.

DK30CH2DPPDU

Triple Monitors USB-C Power Delivery



Expand your Thunderbolt 2 equipped MacBook to dual monitors and connect to additional devices with our **Thunderbolt 2 4K Docking Station**.

TB2DOCK4KDHC

Dual Monitors



This **WiGig Docking Station** gives you the option to dock your laptop wirelessly through WiGig® technology or through a USB-C cable connection.

DKWG30DPPDU

WiGig Technology Dual Monitors

## Multi-port adapters are the perfect on-the-go accessory for laptops



Power and charge your laptop, all while creating an instant work station with our new **USB-C Multi-port Adapter with power delivery**.

DKT30CHPD

4K HDMI USB-C Power Delivery

## USB Hubs

We have the right USB hub for you, whatever your setup and needs.



**4-Port USB 3.0 Hub with Power Delivery - USB-C**  
HB30C4AFPD

4 USBTYPE-A PORTS



**3-Port USB 3.0 Hub plus Gigabit Ethernet - USB-C**  
HB30C3A1GE

3 USBTYPE-A PORTS

**10-Port USB 3.0 Hub with Charge and Sync Ports**  
ST103008U2C



**10-Port USB 3.0 Industrial Hub**  
ST1030USBM



Learn more: [www.startech.com/be/usb-hubs](http://www.startech.com/be/usb-hubs)

# Manage and Expand Your Network

We offer a wide range of networking solutions that make it easy to connect to or expand your network reach.

From upgrading the wireless connection on your laptop to extending a wired signal between buildings, StarTech.com keeps you connected.

## Add performance and reliability to your network.

Our SFPs are not only backed by a lifetime warranty and are fully compliant to MSA standards, but most importantly, match OEM brands in performance and reliability.



### With our SFPs, you get:

- Exact OEM specifications
- MSA and industry standards
- Fully tested products to ensure performance
- Lifetime warranty with technical support
- Cost-savings when compared to OEM SFPs
- A brand you can trust

Cisco compatible 40G QSFP+	QSFP40GLR4ST
HP compatible 10G SFP+	J915OAST
Juniper compatible 10G SFP+	EXSFP10GESRS

See our full line of SFPs:  
[www.startech.com/be/SFPs](http://www.startech.com/be/SFPs)

## Connect to your network with confidence.

Confidently connect your network with our comprehensive line of networking cables.



Our **fibre cables** deliver fast and reliable data transfers over your network.

A50FBLCLC2	10Gb Multimode Duplex Fibre Patch Cable
SMFIBLCLC1	1m Single Mode Duplex Fibre Patch Cable
FIBLCST3	3m Multimode Duplex Fibre Patch Cable



Use our wide range of **CAT6 patch cables** to make PoE-capable Gigabit network connections.

N6PATC3MBL	3m Blue
N6PATC50CMGR	30cm Grey
N6PATC2MGR	2m Grey

### Networking cable features:

- Wide range of connector types and colours
- Various lengths
- Fully tested
- Backed by a lifetime warranty

View the full line of CAT6 and fibre cables:  
[www.startech.com/be/cables/network](http://www.startech.com/be/cables/network)

## Replace, upgrade or add a wired network connection.

Access reliable wired or wireless networks from anywhere with our wide range of laptop network adapters.



1 USB433ACD1X1	USB-A to WiFi
2 US16C30B	USB-C to Gigabit Ethernet
3 USB31000S	USB-C to Gigabit Ethernet

### USB Network adapter features:

- Simple network access for USB equipped devices
- Fast file transfers using true gigabit bandwidth support for gigabit ethernet (GbE) or fast ethernet (10/100) networks
- Extremely portable designs for when you're on the move

See our full line of laptop network adapters:  
[www.startech.com/be/usb-network-adapters](http://www.startech.com/be/usb-network-adapters)

## Scale, manage, or upgrade your network.

Use our selection of switches, extenders and NICs to efficiently manage your network equipment.



Deploy or scale networks by adding eight Gigabit Ethernet ports and two fibre SFP slots with this **Managed Switch**.  
**IES101G2SFPW**



Use our **Gigabit Ethernet Copper-to-Fibre Media Converter** to convert and extend network connections up to 20 km.  
**ET91000SM20**



Upgrade your server or workstation to 10G networking over copper with this **Network Card** that features the powerful Intel X550-AT Chip.  
**ST10000SPEXI**

View the full line of network management solutions:  
[www.startech.com/be/networking-io](http://www.startech.com/be/networking-io)

# Thunderbolt 3: Powerful, Portable, Practical









Thunderbolt™3 is the single-cable I/O technology that can turn your laptop into a powerful workstation. It provides four times the data and twice the video bandwidth of any other cable, up to 100W of system charging, turning port limitations into connection capability.

Thunderbolt 3 is a all-in-one connection that combines every essential technology into a single port. It's the most capable connection to date, and with the right adapters and accessories, it's possibly the most convenient.



Thunderbolt 3 is the USB-C that does it all

## Unprecedented performance

-  2 x 4K @60Hz (or single 5K display)
-  40 Gbps Bandwidth
-  10 GbE network connection between two Thunderbolt 3 computers
-  4x the data and 2x the video bandwidth of any other cable
-  Laptop system charging up to 100W
-  Add any PCIe card to a laptop  
\* via Thunderbolt 3 PCIe chassis


## Universal compatibility

A single port that can connect to Thunderbolt devices, every display (via adapters) and billions of USB devices.

## USB-C connector

Uses the compact and reversible USB-C connector to power and charge a laptop. For more information on USB-C.

## Bandwidth



Thunderbolt 3 products from StarTech.com



## Docking Stations

This **Thunderbolt 3 Dual 4K Docking Station with Power Delivery** maximizes connectivity for your MacBook or Windows laptop.

**TB3DK2DPPDUE**

View more: [www.startech.com/be/tb3-docks](http://www.startech.com/be/tb3-docks)

## With Thunderbolt 3, you can:

- Access and edit large, uncompressed files such as videos and images on the fly, for dynamic on-site production
- Transfer a 4K movie in under 30 seconds, or 3 hours of 4K GoPro® video in less than a minute
- Edit 4K video on one display, with a full-size video preview on the second 4K display
- Dock and undock quickly, with a single cable for peripherals, dual 4K monitors, and laptop charging
- Daisy chain up to six devices

## Display Adapters

Connect a MacBook Pro or Windows Thunderbolt 3 laptop to dual 4K displays at 60Hz with our **Thunderbolt 3 to Dual DisplayPort Adapter.**

**TB32DP2T**

View more: [www.startech.com/be/tb3-adapters](http://www.startech.com/be/tb3-adapters)



## Cables and Adapters

Our **Legacy Adapter** allows connections from a Thunderbolt 3 laptop to Thunderbolt 1 and 2 devices.

**TBT3TBTADAP**

View more: [www.startech.com/be/tb3-cables](http://www.startech.com/be/tb3-cables)







# Experience the Performance of USB-C

A new connector has arrived for computers, peripherals, and mobile devices, the USB-C connector. Also known as USB Type-C, it's much more than just USB. Unlike its predecessors, the USB-C connector offers an array of benefits:



This **USB-C Triple Video Docking Station** enables you to connect to three 4K monitors, while charging your laptop.

**DK30CH2DPPDU**



## Supports multiple technologies.

Perhaps the most important shift with USB-C is the ability to accommodate Alternate Modes. The Alt Mode spec allows for DisplayPort, HDMI, and Thunderbolt 3 protocols to be transferred over a USB connection.

## Powers and charges your laptop.

USB-C can deliver up to 100W of power to compatible laptop systems. This makes it perfect for tablets and laptops.

## More bandwidth.

The connector supports bandwidths of 10Gbps using USB 3.1, and 40Gbps using Thunderbolt 3. For more information on Thunderbolt 3.

## Compact design and reversible.

The USB-C connector features a uniquely compact design that's perfect for any device (including mobile devices) and is reversible, which makes for easier connections.



**USB-C Multiport Adapter** with native video support, GbE and USB 3.0 ports.  
**DKT30CHPDW**



Our unique **Presentation Adapters**, prevent your laptop from entering sleep mode during a presentation.

**HDMI** CDP2HD4K60SA  
**VGA** CDP2VGASA



USB-C supports USB 2.0 and USB 3.0 with the use of this **USB-C to USB-A Adapter**.  
**USB31CAADP**



Take advantage of USB 3.1 10 Gbps speeds with this **USB-C to 2.5" SATA Adapter**.  
**USB31CSAT3CB**

Given its capabilities, USB-C will be the world's most prevalent connector in the years to come. In fact, many popular laptops and phones have already switched to, or added USB-C ports.

With the most comprehensive product offering for USB-C connectivity, as well as trusted support worldwide, StarTech.com makes it easy to connect any USB-C device.

# Modern Meeting Rooms

## Meet Convenient Connectivity

Set up a meeting space that will help you and your coworkers have seamless meetings and presentations.



### Connect a laptop

The new **Presentation Adapter** is a unique accessory designed with the boardroom in mind.

- 1 Equipped with a "Presentation Mode" switch, this **USB-C Display Adapter** keeps your computer awake during long presentations.

HDMI CDP2HD4K60SA VGA CDP2VGASA



Conveniently connect any laptop to an HDMI display or projector.

With the transition to USB-C laptops, make sure old and new models can connect with ease with our **Boardroom HDMI Converter Cable**.  
CMDPHD2HD

USB-C, HDMI, MINI DISPLAYPORT



Cut down on clutter with this all-in-one solution.

- 2 The **Conference Table Box** enables a variety of A/V connectivity options like VGA, HDMI, and Mini DisplayPort.  
BOX4HDECP



### Mount a display NEW PRODUCT LINE

Mount high value large-screen displays with confidence using our new **TV Wall Mounts**.



- 3 **32" to 70" TV Wall Mount** FLATPNLWALL  
**Full Motion TV Wall Mount** FPWARTB2  
**Ceiling TV Mount** FLATPNLCEIL

### Keep it charged

Charge multiple mobile devices at once.

- 4 **7-Port USB Charging Station**. ST7CU35122



### No boardroom is complete without the ability to connect.

Our high-quality HDMI or DisplayPort cables connect any device, can be routed through the wall and reduce overall clutter in the boardroom.



- HDMM15M 15m HDMI Cable
- HDMM30MA 30m Active HDMI Cable
- DISPL15MA 15m Active DisplayPort Cable

# Must-Have Road Warrior Tools

Simple connectivity solutions make business travel easy. Check out our must-have accessories designed for mobility, making connections easy for road warriors everywhere.

## On-the-go productivity

Setup a functional workstation wherever you are and connect to HDMI or VGA display, GbE and USB-A with a **USB Multi-Port Adapter**.

- 1 USB-C to HDMI or VGA, USB 3.0, GbE DKT30CHV
- 2 USB 3.0 to HDMI or VGA, USB 3.0, GbE USB3SMDOCKHV
- 3 USB-C to HDMI, USB-A, USB-C CDP2HDUACP



1



2



3

USB-C Power Delivery

## Convenient connectivity for painless presentations

Our **Travel A/V Adapters** allow you to connect your laptop to virtually any projector or monitor.



USB-C to VGA, DVI or HDMI  
CDPVGDVHDB



HDMI to DisplayPort, VGA, or DVI  
HD2DPVGADVI



Mini DisplayPort to VGA, DVI or HDMI  
MDPVGDVHD4K




DisplayPort to VGA, DVI or HDMI  
DP2VGDVHD

## Power, charge & access devices

Charge and sync your phone, tablet and other devices with our wide range of charging cables.



- USBLT1MWS LIGHTNING
- USB2AC2M USB-C
- LTUB1MBK LIGHTNING / MICRO USB
- USB31C5C1M USB-C | POWER DELIVERY



## USB-C Product Finder

From simple to high-performance connectivity requirements, our solutions make it easy to make the most of your USB-C equipped devices.



### Did you know?

USB-C peripherals also work in your laptop's Thunderbolt 3 port

Display Adapters and Cables					
Part Number	Connector Type	Max Resolution	Format	Colour	Power Delivery
CDP2DP	USB-C to DP	4K 60Hz	Adapter	●	
CDP2DPW			Adapter	○	
CDP2DPMM1MB			Cable - 1m	●	
CDP2DPMM6B			Cable - 1.8m	●	
CDP2DVI	USB-C to DVI	1920x1200	Adapter	●	
CDP2DVIW			Adapter	○	
CDP2DVIMM1MB			Cable - 1m	●	
CDP2DVIMM2MB			Cable - 2m	●	
CDP2HD4K60	USB-C to HDMI	4K 60Hz	Adapter	●	✓
CDP2HD4K60SA ★			Adapter	●	
CDP2HD4K60W			Adapter	○	
CDP2HDUCP			Adapter	●	
CDP2HDUCPW		Adapter	○		
CDP2HD		4K 30Hz	Adapter	●	
CDP2HDMM1MB			Cable - 1m	●	
CDP2HDMM2MB			Cable - 2m	●	
CDP2HDW		1920x1200	Adapter	○	
CMDPHD2H		USB-C/HDMI/mDP to HDMI	4K 30Hz	Cable - 2m	
CDP2VGA	USB-C to VGA	1920x1200	Adapter	●	✓
CDP2VGAMM1MB			Cable - 1m	●	
CDP2VGAMM2MB			Cable - 2m	●	
CDP2VGASA ★			Adapter	●	
CDP2VGAUCP			Adapter	●	
CDP2VGAUCPW			Adapter	○	
CDP2VGAW			Adapter	○	

★ Presentation Mode

Multiport and Travel A/V Adapters								
Part Number	HDMI	VGA	DVI	mDP	USB Hub Ports	Gigabit Ethernet	Power Delivery	Colour
CDPVGDVHDB	✓	✓	✓					●
CDPVGDVHDBP	✓	✓	✓					●
CDPVGDVHDMDP	✓	✓	✓	✓				○
DKT30CHPD	✓				2	✓	✓	●
DKT30CHPDW	✓				2	✓	✓	○
CDP2HDUACP	✓				✓		✓	●
CDP2HDUACPW	✓				✓		✓	○
CDP2VGAUACP		✓			✓		✓	●
DKT30CHV	✓	✓			✓	✓		●
DKT30CDVPD			✓		✓	✓	✓	○
DKT30CHD	✓				✓	✓		●
DKT30CHVW	✓	✓			✓	✓		○

Docking Stations									
Part Number	Displays	Video Outputs	4K Support	Power Delivery	Number of USB Ports	Gigabit Ethernet	Fast Charge USB Port(s)	OS Support	Colour
DKWG30DPHPDU	2	DisplayPort HDMI	Single Monitor (4K 30Hz) <small>when connected by USB-C</small>	Yes (60W; USB-C only)	2xUSB-A(3.0) /2x USB-A (2.0)			Windows®	●
DK30CH2DPPD	2	2x DisplayPort HDMI	Dual DP 4K 60Hz + HDMI 4K 30Hz	Yes (60W)	4xUSB-A / 1xUSB-C	✓	✓	Windows® macOS	●
MST30C2DPPD	2	DisplayPort HDMI	Single Monitor (4K 30Hz)	Yes (60W)	3xUSB-A / 1xUSB-C			Windows®	●
DK30BACDD	2	DVI HDMI VGA	✗		5xUSB-A			Windows® Chrome OS™	●



## USB-C Product Finder

From simple to high-performance connectivity requirements, our solutions make it easy to make the most of your USB-C equipped devices.

Hubs						
Part Number	USB Ports	Fast Charge Port (s)	Gigabit Ethernet	Power Delivery	Colour	Power Source
HB30C3A1GE	3x USB-A		✓		●	Optional AC Adapter Included
HB30C4AFS	4x USB-A	4x Charge & Sync Ports			●	
HB30C3A1CFS	3x USB-A 1x USB-C	3x Charge & Sync Ports			●	
HB30C1A1CPD	1x USB-A 1x USB-C			✓	●●	USB-Powered
HB30C3A1CFBW	3x USB-A 1x USB-C				○	
HB30C3A1CFB	3x USB-A 1x USB-C				●	
HB30C3AGEPD	3x USB-A		✓	✓	●	
HB30C3APD				✓	●	
HB30C3APDW				✓	○	
HB30C3A1GEA			✓		○	
HB30C4AFPD	4x USB-A			✓	●	
HB30C4AB					●	
HB30C4ABW					○	

Gigabit Ethernet Adapters					
Part Number	Gigabit Ethernet	USB Ports	Power Delivery	Colour	
US1GC30PD	1		✓	●	
US1GC303APD		3	✓	●	
US1GC301AU		1		●	
US1GC30A				●	
US1GC30B				●	
US1GC30W				○	
US1GC301AU2R		2	1		●

Note: All StarTech.com USB-C Gigabit Ethernet Adapters are Thunderbolt 3 Port compatible.

Drive Enclosures					
Part Number	Bus Type	Drive Type	Number of Drives	Max Drive Height	Special Features
SMS2BU31C3R	USB 3.1 Gen 2 - 10 Gbps	mSATA	2		RAID
S252BU313R				12.5 mm	RAID & Fan
S251BPU31C3		2.5in SATA	1	9.5 mm	
S251BU31315				15 mm	
S251BU31C3CB				9.5 mm	
SM21BMU31C3		M.2 (NGFF; B-Key)			

Card Reader/Writers					
Part Number	Bus Type	SD	Micro SD	CFast	CompactFlash
2SD4FCRU3C	USB 3.0 (5 Gbps)	Dual Slot			
CFASTRWU3C	USB 3.0 (5 Gbps)			✓	
FCREADU3C	USB 3.0 (5 Gbps)	✓	✓		✓
SDMSDRWU3AC	USB 3.0 (5 Gbps)	✓	✓		

Thunderbolt 3 Cables						
Part Number	Thunderbolt 3 Transfer Speed	Length	Colour	USB Version	DisplayPort Alt Mode Support	Power Delivery Capabilities
TBLT34MM50CM	40Gbps	0.5m	●	USB 3.1 Gen 2 - 10 Gbps	✓	100W
TBLT34MM50CW			○			
TBLT3MM1M	20Gbps	1m	●	USB 3.1 Gen 2 - 10 Gbps	✓	60W
TBLT3MM1MW			○			100W
TBLT3MM2M	20Gbps	2m	●	USB 3.1 Gen 1 - 5 Gbps	✓	60W
TBLT3MM2MW			○			
TBLT3MM1MA	40Gbps	1m	●	USB 3.1 Gen 2 - 10 Gbps	✗	100W
TBLT3MM2MA		2m	●			USB 3.1 Gen 1 - 5 Gbps

Thunderbolt 3 cables can be used as USB-C cables at USB speeds.



## Display Mount Finder

See our wide range of display mounts and find the right one for your work area.



## Docking Station Finder

Find your perfect match from our broad selection of universal docking stations.

Part Number	Displays	Type	Articulating Arm	Height Adjustment	Max Monitor Size	Colour
ARMSLIM		Desk Mount	✓	Spring-Assisted	26in	●
ARMPIVOTB			✓	Adjust Along Pole	27in	●
ARMPIVOTE			✓	Spring-Assisted	24in	●
ARMPIVOTH			✓		32in	●
ARMPIVOT			✗	Adjust Along Pole	30in	●
ARMPIVOTV2			✗		32in	●
ARMPIVSTND		Desktop Stand	✗	Adjust Along Pole	30in	●
ARMPIVWALL		Wall-Mount	✓	Spring-Assisted	30in	●
ARMWALLDS			✓	✗	27in	●
ARMWALLS			✓		27in	●
ARMWALL			✗		27in	●
ARMCBCL			Cubicle Wall Hanger	✗	Adjust Along Pole	30in
MONSTADJD		Monitor Riser	✗	Modular	32in	●
MONSTADJDL			✗		32in	●
ARMUNONB			Desk Mount	✓	Spring-Assisted	27in
ARMDUAL		Desk Mount	✓	Adjust Along Pole	24in	●
ARMSLIMDUO			✓	Spring-Assisted	30in	●
ARMBARDUO		Desktop Stand	✗	Adjust Along Pole	24in	●
ARMDUAL30		Desk Mount	✓	Spring-Assisted	30in	●●
ARMDUALV		Desk Mount	✗	Adjust Along Pole	27in	●
ARMBARDUOV	Desktop Stand	✗	27in		●	
ARMTRIO		Desk Mount	✓	Adjust Along Pole	24in	●
ARMBARTRIO		Desktop Stand	✓		27in	●
ARMQUAD		Desk Mount	✓	Adjust Along Pole	27in	●
ARMBARQUAD		Desktop Stand	✓		27in	●

Thunderbolt 3								
Part Number	Displays	Video Outputs	4K	Power Delivery	Number of USB & Other Ports	Fast Charge USB port(s)	Style	
TB3DKDPMWUE		DisplayPort, Thunderbolt 3 (USB-C)	Dual 4K 60Hz	15W (MacBook Pro only)	2xUSB-A / 1xUSB-C	✓	Horizontal Grey and Black	
TB3DK2DPWUE				✗				
TB3DK2DPPDUE				Yes (85W)				
USB-C (5 Gbps)								
DK30BACDD		DVI, HDMI, VGA	✗	✗	5x USB-A	✓	Vertical or Horizontal Black & Silver	
MST30C2DPPD		DisplayPort, HDMI	Single Monitor (4K 60Hz)	Yes (60W)	3xUSB-A / 1xUSB-C		Horizontal Black	
DK30CH2DPPDU		2x DisplayPort, HDMI	Dual DP 4K 60Hz + HDMI 4K 30Hz		4xUSB-A / 1xUSB-C	Horizontal Black & Silver		
WiGig or USB-C								
DKWG30DPHPDU		DisplayPort, HDMI	Single Monitor (4K 30Hz) - when connected by USB-C	Yes (60W; USB-C only)	2xUSB-A(3.0) / 2x USB-A (2.0)	✓	Vertical Black & Silver	
USB 3.0 - A (5 Gbps)								
USB3VDOCK4DP		DisplayPort	Single Monitor (4K 30Hz)	✗	3xUSB-A	✓	Horizontal Black & Silver	
USB3VDOCKD		DVI	✗		3xUSB-A		Horizontal Black & Silver	
USB3VDOCKH		HDMI	✗		3xUSB-A	Horizontal Black & Silver		
USB3DOCKHDPC		DisplayPort, HDMI	Single Monitor (4K 30Hz)		4xUSB-A	Horizontal Black		
USB3SDOCKDD		2x DVI, HDMI, VGA	✗		5xUSB-A	Vertical or Horizontal Black & Silver		
USB3SDOCKHHD		HDMI, DVI, VGA	✗		2xUSB-A(3.0) / 4x USB-A (2.0)	✗	Vertical Black	
USB3SDOCKHDV		HDMI, DVI, VGA	✗		3xUSB-A	Horizontal Black		
USB3DOCKH2DP		2x DisplayPort, HDMI	Single Monitor (4K 30Hz)		5xUSB-A	✓	Horizontal Black & Silver	
USB 3.0 - A (5 Gbps) - 2x Laptops								
USB3DDOCKFT		DisplayPort, HDMI	Single Monitor (4K 30Hz)		✗	5xUSB-A	✓	Horizontal Black & Silver
Thunderbolt 2								
TB2DOCK4KDHC		HDMI, Mini DisplayPort, Thunderbolt	Single Monitor (4K 60Hz)	✗	4xUSB-A	✓	Horizontal Silver	
TB2DOCK4K2DP		2x DisplayPort, Mini DisplayPort, Thunderbolt			4xUSB-A	Horizontal Silver		

3000+ products supporting over 200 different technologies

USB-C · Thunderbolt 3 · DisplayPort · HDMI · HDBaseT · SFP · RJ-45 · SATA · Bluetooth · Apple Lightning

## Cables

A/V  
Networking  
USB-C & Thunderbolt 3  
Charging



## Display Adapters

USB-C & Thunderbolt 3  
USB-A  
DisplayPort & Mini DisplayPort  
HDMI & DVI



## Networking

SFP Transceivers  
Laptop Network Adapters  
Desktop & Server Network Cards  
Ethernet Media Converters



## Display Mounts & Ergonomics

Workstation Mounts  
Boardroom Mounts  
Ergonomic Furniture



## Data Storage

Data Recovery, Imaging, Sanitizing  
Internal & External Storage  
Converters & Adapters



## A/V Connectivity

Extenders  
Converters & Scalers  
Splitters & Switchers  
Video Capture



## Universal Docking Stations

USB-A Universal Docking Stations  
USB-C & Thunderbolt  
Multi-Port Adapters




## KVM Switches & Cables

Desktop & Enterprise KVM Switches  
KVM Extenders  
KVM Cables



## Racks & Enclosures

Rack Shelves & Accessories  
Wall-Mount Racks & Enclosures  
Open Frame Racks & Enclosures



## Cards & Peripherals

Serial Cards, Adapters, Extenders  
Desktop Connectivity  
USB Cards & Extenders  
USB-A Hubs  
USB-C & Thunderbolt Hubs

