

Desktop KVM

VGA, DVI, HDMI, and DisplayPort KVMs

A huge selection of KVMs including unique multi-monitor versions for demanding multimedia applications.



2 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub
SV231DD2DUA

MULTI-MONITOR KVMs

# of Ports	Input Interface	Video	Audio	Part Number
2, 4 Ports	PS/2	VGA + VGA, Dual Monitor	No	SV221DD/SV421DD
2, 4 Ports	USB	DVI + DVI, Dual Monitor	Yes	SV231DD2DUA/SV431DD2DUA
2, 4 Ports	USB	VGA + DVI, Dual Monitor	Yes	SV231DDVDUA/SV431DDVDUA
2 Ports	USB	DVI + DVI + DVI + DVI, Quad Monitor	Yes	SV231QDVIUA




4 Port High Resolution DVI Dual Link KVM Switch with Audio
SV431DVIUAHR

USB KVMs

# of Ports	Input Interface	Video	Audio	Features	Part Number
2 Ports	USB	VGA	Yes	Ultra compact on a cable	SV215MICUSBA
2 Ports	USB	DVI	Yes	Ultra compact on a cable	SV215MICDVI
2, 4 Ports	USB	VGA	Yes	Kit with cables	SV211KUSB/SV411KUSB
2, 4 Ports	USB	DVI	Yes	Kit with cables	SV211KDVI
2, 4 Ports	USB	VGA	No	Professional Series	SV231USB/SV431DUSBU
4 Ports	USB	VGA	Yes	Professional Series	SV431USBA
2, 4 Ports	USB	VGA	Yes	Built-in Ethernet Network Hub	SV231USBAN/SV431USBAN
2, 4 Ports	USB	DVI	Yes	Built-in USB 2.0 hub	SV231UADVI/SV431UADVI
2, 4 Ports	USB	DVI Dual-Link	Yes	High resolution 2560x1600	SV231DVIUAHR/SV431DVIUAHR

Ideal for switching between a PC and Notebook



DISPLAYPORT KVMs

Description	Part Number
2 Port DisplayPort KVM (Digital Audio only)	SV231DPU
2 Port DisplayPort KVM (Digital & Analog Audio)	SV231DPUA
4 Port DisplayPort KVM (Digital & Analog Audio)	SV431DPUA

PS/2 KVMs

# of Ports	Input Interface	Video	Features	Part Number
2 Ports	PS/2	VGA	Ultra compact on a cable	SV211MICRO
2 Ports	PS/2	VGA	Kit with cables	SV211K
2, 4 Ports	PS/2	DVI	Professional Series	SV221DVI/SV421KDVI
2, 4 Ports	PS/2	VGA	Professional Series	SV231/SV431

UNIVERSAL KVM CABLES

Length	KVM Connectors	PC Connectors	Part Number
6, 10, 15ft	USB+VGA	USB+VGA	SVUSB2N1_x
6, 15ft	USB+DVI+SPKR+MIC	USB+DVI+SPKR+MIC	USBDVI4N1Ax
6, 10, 15ft	DB15	USB+VGA	SVECONUSx
6, 10, 15, 25, 50ft	DB15	PS/2+VGA	SVECONx
6, 10, 15, 25, 35, 50ft	PS/2+VGA	PS/2+VGA	SVPS23N1_x
6, 10, 15, 25, 50ft	PS/2+VGA	PS/2+VGA	PS23N1THINx

x = Length

For additional KVMs, dongles, accessories, and a large selection of KVM cables of varying lengths, please visit our website at www.startech.com/kvm

QUESTIONS?

PHONE

1-800-265-1844

LIVE CHAT

www.startech.com



StarTech.com

Hard-to-find made easy®

Enterprise KVM & LCD Consoles

Server Room Solutions

Solutions for taking full control of the server room, including local, long distance, and full remote over IP.



Rackmount, IP, and Matrix KVMs

A full line of LCD Consoles and versatile enterprise level KVM switches, from standard cabled rackmount models to multi-user matrix IP KVMs.



4 Port USB VGA IP KVM Switch with Virtual Media SV441DUSBI

Control multiple servers or KVMs remotely. Supporting VGA and USB, as well as virtual media means not only can you control your machines remotely, but have full access for remote software or operating system installations.

RACKMOUNT KVM

# of Ports	Extra Features	Part Number
8 Ports	RackMount	SV831DUSBU
8 Ports	Audio Support	SV831DUSBAU
16 Ports	RackMount	SV1631DUSBU



1 Port IP KVM with Virtual Media SV1107IPEXT

IP KVMs

# of Ports	Simultaneous Users	Extra Features	Part Number
1 Port	1	Virtual Media	SV1107IPEXT
1 Port	1	Virtual Media Plus Serial, USB & PS/2	SV1115IPEXT
8, 16 Ports	1	RackMount	SV841HDIE/SV1641HDIE
16, 32 Ports	3 (Matrix)	Virtual Media, Serial, USB & PS/2	SV1653DXI/SV3253DXI
16, 32 Ports	4 (Matrix)	Virtual Media, Serial, USB & PS/2	SV1654DX4I/SV3254DX4I

LCD, KVM and IP KVM Consoles

A full range of LCD sizes from 15in to an industry leading 20in, with connectivity for VGA & DVI, and configurations from 1 to 16 ports.

LCD CONSOLES - ENTRY LEVEL

# of Ports	Size	Part Number
1 Port	17in	RACKCONV1701
1 Port	19in	RACKCONV1901

LCD CONSOLES - PROFESSIONAL SERIES

# of Ports	Size	Part Number
1 Port	17in	RACKCONS1701
1 Port	19in	RACKCONS1901
8 Ports	17in	RACKCONS1708
16 Ports	17in	RACKCONS1716
16 Ports	19in	RACKCONS1916



1U 20in High Resolution Folding Rack Mount LCD Console for 19in Rack RACKCONS2001

For maximum control and usability, the RACKCONS2001 supports both DVI and VGA servers and KVMs, and boasts the largest screen size (20.1in), and highest resolution (1600x1200) screen available in a rack mountable LCD Console.

LCD CONSOLE WITH BUILT-IN CONTROL OVER IP

# of Ports	Size	Part Number
16 Port	17in	CABCONS1716I



KVM Console to USB 2.0 Portable Laptop Crash Cart Adapter NOTECONS01

With the NOTECONS01, your laptop quickly becomes a portable console allowing you to connect to and control any PC or headless server with a VGA and USB port.

In the News

"StarTech.com's USB KVM may be your new best friend for trips to the datacenter... you can use this from the back of the rack. So if you are handling issues that require moving cables or network connections this can be a major timesaver." - everythingUSB.com

QUESTIONS?

PHONE

1-800-265-1844

LIVE CHAT

www.startech.com



StarTech.com

Hard-to-find made easy®