



HDMI Signal Extender

HDMIEXT

Introduction

Thank you for purchasing a StarTech.com HDMI Signal Extender. This product allows you to boost and extend the length of HDMI signals over a copper based HDMI cable by 12 meters at 1080p / UXGA (24 meters in total extension).

Features

- Extends HDMI transmission range by 12 meters, without degradation
- HDCP 1.1 compliant
- Plug and Play, easy to install

Before You Begin

System Requirements

- An HDMI video Source
- Input and Output HDMI cables
- A display with at least 1 HDMI input

Basic Setup

Connecting the video source to the extender:

Connect the HDMI cable running from your video source to the **HDMI INPUT** port on the back of the video extender.

Connecting the extender to the display:

Insert a standard HDMI cable into the **HDMI OUTPUT** port. Insert the opposite end of the cable into your video display.

Powering the extender:

Connect the tip on the power adapter (provided) to the port marked **DC/5V 2A** on the video extender. Connect the opposite end to a wall outlet or other suitable power source.

The red light located above the power input will illuminate, indicating that your extender is functioning.

Accessories

ZENHDMI2

6.6 ft (2m) HDMI Digital Audio/Video Cable

ZENHDMI1

3.3 ft (1m) HDMI Digital Audio/Video Cable

ZENHDMI4

13.1 ft (4m) HDMI Digital Audio/Video Cable

Specifications

Video Input	1 x HDMI
Video Output	1 x HDMI
Dimensions (LxWxH)	105 x 76 x 30mm
Weight	1.35 lbs
Power	DC 5V, 2A
Certification (Regulatory)	FCC, CE

Support, Warranty Information, and Regulatory Compliance Statement

If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads. This product is backed by a one-year warranty. In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability: In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

FCC Compliance Statement: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.