

5 Channel PCI Sound Adapter Card with AC97 3D Audio Effects

PCISOUND5CH



*actual product may vary from photos

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

Table of Contents

Introduction	1
Packaging Contents	1
System Requirements.....	1
Installation	2
Installation	3
Hardware Installation	3
Driver Installation.....	4
Software Installation (optional)	4
Jumper Configuration	4
Specifications	5
Technical Support	6
Warranty Information	6

Introduction

This StarTech.com 5 Channel PCI Sound Card offers a cost-effective multimedia solution, delivering high quality 5.1 channel audio that's ideal for gaming, HTPC applications or any surround sound configuration. Providing true Full-Duplex playback/capture with different sampling rates (up to 48KHz stereo), the PCI sound card supports simultaneous recording and playback, and features a GAME/MIDI port that lets you use a Serial joystick or other gaming device.

Packaging Contents


- 1 x PCISOUND5CH adapter card
- 1 x Driver Installation CD
- 1 x Instruction Manual

System Requirements


- PCI (5V) enabled computer system with available slot
- Speaker system with 3.5mm mini-jack interface
- Microsoft® Windows® 2000/XP/Vista/7

Installation

External View



Internal View



Installation

WARNING! PCI cards, like all computer equipment, can be severely damaged by static electricity. Be sure that you are properly grounded before opening your computer case or touching your PCI card. StarTech.com recommends that you wear an anti-static strap when installing any computer component. If an anti-static strap is unavailable, discharge yourself of any static electricity build-up by touching a large grounded metal surface (such as the computer case) for several seconds. Also be careful to handle the PCI card by its edges and not the gold connectors.

Hardware Installation

1. Turn your computer off and any peripherals connected to the computer (i.e. Printers, external hard drives, etc.). Unplug the power cable from the rear of the power supply on the back of the computer.
2. Remove the cover from the computer case. Refer to documentation for your computer system for details.
3. Locate an open PCI or slot and remove the metal cover plate on the rear of the computer case.
4. Insert the card into the open PCI or PCI-X slot and fasten the card's bracket to the rear of the case.

OPTIONAL: To connect an existing CD-ROM drive's analog audio signal to the sound card, use an appropriate audio cable (supplied with CD-ROM drive) from the audio output on the CD-ROM drive to one of the input headers on the card. Connect to the appropriate header, depending on the make of CD-ROM (i.e. Sony, Panasonic or AUX/Other).

5. Place the cover back onto the computer case.
6. Insert the power cable into the socket on the power supply and reconnect all other connectors removed in Step 1.

Driver Installation

Windows 2000/XP/Vista/7

1. After restarting your computer, a message should appear indicating that Windows has detected a hardware change. Click the Next button to continue with the installation.
2. Put the CD entitled Drivers and Utility - Installation into your CD-ROM drive.
3. Select Specify the location of the driver (Advanced), followed by the Next button.
4. Select Specify a location and click the Browse button to designate the location of the necessary files. Once the Browse for Folder window appears, select the drive designated for your CD-ROM drive. Open the "CMEDIA" folder, followed by "\CMEDIA\CMi8738-6CH".
5. Open the appropriate folder, followed by the "DRV" folder.
6. Click OK. Once Windows has located the driver, click the Next button. Following this, the installation is automated. Follow the Windows prompts to finish installation.


Software Installation (optional)

1. On the Installation CD, navigate to the "CMEDIA/CMi8738-6CH" folder and then the appropriate operating system version, then under the "APP" folder.
2. Double-click on SETUP.EXE software installation file, and follow all the prompts to complete the installation.


Jumper Configuration

The jumper setting for Center/Sub configuration simply reverses the center/sub channels on the cable. Change the jumper setting if you find the Center/Sub channels reversed on the audio receiver/speakers.

Option A



Option B



Specifications

Bus Interface	PCI (5V)
External Connectors	5 x 3.5mm mini-jack (Line In, Mic In, Front Out, Rear Out, Center/Sub) 1 x Game/MIDI
Internal Connectors	2 x 4-pin CD-ROM In header (Sony, Panasonic) 1 x 4-pin AUX In header
Chipset ID	CMedia CMI8738
Duplex Mode	Full Duplex
Maximum Sampling Rate	48KHz (Playback/Recording)
Compatible Operating Systems	Windows 2000/XP/Vista/7

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a lifetime warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.