



USB-C Product Finder

From simple to high-performance connectivity requirements, our solutions make it easy to make the most of your USB-C equipped devices.

Display Adapters and Cables

Part Number	Connector Type	Max Resolution	Format	Color	Power Delivery	
CDP2DP	USB-C to DP	4K 60Hz	Adapter	●		
CDP2DPW			Adapter	○		
CDP2DPMM1MB			Cable - 1m (3 ft)	●		
CDP2DPMM6B			Cable - 2m (6 ft)	●		
CDP2DVIW	USB-C to DVI	1920x1200	Adapter	●		
CDP2DVIMM1MB			Adapter	○		
CDP2DVIMM2MB			Cable - 1m (3 ft)	●		
CDP2DVIMM2MB			Cable - 2m (6 ft)	●		
CDP2HD4K60	USB-C to HDMI	4K 60Hz	Adapter	●		
CDP2HD4K60SA ★			Adapter	●		
CDP2HD4K60W			Adapter	○		
CDP2HDUCP			Adapter	●		✓
CDP2HDUCPW			Adapter	○		
CDP2HD		4K 30Hz	Adapter	●		
CDP2HDMM1MB			Cable - 1m (3 ft)	●		
CDP2HDMM2MB			Cable - 2m (6 ft)	●		
CDP2HDW			1920x1200	Adapter		○
CMDPHD2H		USB-C/HDMI/mDP to HDMI	4K 30Hz	Cable - 2m (6 ft)	●	
CDP2VGA	USB-C to VGA	1920x1200	Adapter	●		
CDP2VGAMM1MB			Cable - 1m (3 ft)	●		
CDP2VGAMM2MB			Cable - 2m (6 ft)	●		
CDP2VGASA ★			Adapter	●		
CDP2VGAUCP			Adapter	●		✓
CDP2VGAUCPW			Adapter	○		
CDP2VGAW			Adapter	○		

★ Presentation Mode

Talk to a Tech Advisor [1.800.265.1844](tel:1.800.265.1844) www.startech.com/chat

StarTech.com



Did you know?

USB-C peripherals also work in your laptop's Thunderbolt 3 port

Multiport and Travel A/V Adapters

Part Number	HDMI	VGA	DVI	mDP	USB Hub Ports	Gigabit Ethernet	Power Delivery	Color
CDPVGDVHDB	✓	✓	✓					● ●
CDPVGDVHDBP	✓	✓	✓					●
CDPVGDVHDMDP	✓	✓	✓	✓				○
DKT30CHPD	✓				2	✓	✓	●
DKT30CHPDW	✓				2	✓	✓	● ○
CDP2HDUACP	✓				✓		✓	●
CDP2HDUACPW	✓				✓		✓	○
CDP2VGAUACP		✓			✓		✓	●
DKT30CHV	✓	✓			✓	✓		●
DKT30CDVPD			✓		✓	✓	✓	○
DKT30CHD	✓				✓	✓		●
DKT30CHVW	✓	✓			✓	✓		● ○

Docking Stations

Part Number	Displays	Video Outputs	4K Support	Power Delivery	Number of USB Ports	Gigabit Ethernet	Fast Charge USB Port(s)	OS Support	Color
DKWG30DPPD		DisplayPort HDMI	Single Monitor (4K 30Hz) when connected by USB-C	Yes (60W; USB-C only)	2xUSB-A(3.0) /2x USB-A (2.0)			Windows®	● ●
DK30CH2DPPD		2x DisplayPort HDMI	Dual DP 4K 60Hz + HDMI 4K 30Hz	Yes (60W)	4xUSB-A / 1xUSB-C			Windows® macOS	● ●
MST30C2DPPD		DisplayPort HDMI	Single Monitor (4K 30Hz)	Yes (60W)	3xUSB-A / 1xUSB-C	✓	✓	Windows®	●
DK30BACDD		DVI HDMI VGA	✗		5xUSB-A			Windows® Chrome OS™	● ●

Hubs						
Part Number	USB Ports	Fast Charge Port (s)	Gigabit Ethernet	Power Delivery	Color	Power Source
HB30C3A1GE	3		✓		●	Optional AC Adapter Included
HB30C4AFS	4	3x Charge & Sync Ports			●	
HB30C3A1CFS	3x USB-A 1x USB-C	3x Charge & Sync Ports			●	
HB30C1A1CPD	1x USB-A 1x USB-C			✓	●●	USB-Powered
HB30C3A1CFBW	3x USB-A 1x USB-C				○	
HB30C3A1CFB	3x USB-A 1x USB-C				●	
HB30C3AGEPD	3		✓	✓	●	
HB30C3APD				✓	●	
HB30C3APDW				✓	○	
HB30C3A1GEA			✓		○	
HB30C4AFPD	4			✓	●	
HB30C4AB					●	
HB30C4ABW					○	

Gigabit Ethernet Adapters					
Part Number	Gigabit Ethernet	USB Ports	Power Delivery	Color	
US1GC30PD	1		✓	●	
US1GC303APD		3	✓	●	
US1GC301AU		1			●
US1GC30A					●
US1GC30B					●
US1GC30W					○
US1GC301AU2R		2	1		●

Note: All StarTech.com USB-C Gigabit Ethernet Adapters are Thunderbolt 3 Port compatible.

Drive Enclosures

Part Number	Bus Type	Drive Type	Number of Drives	Max Drive Height	Special Features
SMS2BU31C3R	USB 3.1 Gen 2 - 10 Gbps	mSATA	2	Full Size - 50.8 mm Half Size - 26.8 mm	RAID
S252BU313R		2.5in SATA		12.5 mm	RAID & Fan
S251BPU31C3			1	9.5 mm	
S251BU31315				15 mm	
S251BU31C3CB				9.5 mm	
SM21BMU31C3		M.2 (NGFF; B-Key)		80 mm	

Card Reader/Writers

Part Number	Bus Type	SD	Micro SD	CFast	CompactFlash
2SD4FCRU3C	USB 3.0 (5 Gbps)		2		
CFASTRWU3C	USB 3.0 (5 Gbps)			✓	
FCREADU3C	USB 3.0 (5 Gbps)	✓	✓		✓
SDMSDRWU3AC	USB 3.0 (5 Gbps)	✓	✓		

Thunderbolt 3 Cables

Part Number	Thunderbolt 3 Transfer Speed	Length	Color	USB Version	DisplayPort Alt Mode Support	Power Delivery Capabilities
TBLT3MM2MW	40Gbps	0.5m	●	USB 3.1 Gen 2 - 10 Gbps	✓	100W
TBLT34MM50CW			○			
TBLT3MM1M	20Gbps	1m	●	USB 3.1 Gen 2 - 10 Gbps	✓	60W
TBLT3MM1MW			○			100W
TBLT3MM2M	20Gbps	2m	●	USB 3.1 Gen 1 - 5 Gbps	✓	60W
TBLT3MM2MW			○			
TBLT3MM1MA	40Gbps	1m	●	USB 3.1 Gen 2 - 10 Gbps	✗	100W
TBLT3MM2MA		2m	●	USB 3.1 Gen 1 - 5 Gbps		60W

Thunderbolt 3 cables can be used as USB-C cables at USB speeds.