

Component Wall Plate Video Extender over Cat 5 with Audio

CPNTUTPWALLA

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

*actual product may vary from photos

Packaging Contents

- 2 x CPNTUTPWALLA units
- 2 x Screw kit
- 1 x Instruction Manual

System Requirements

- yPbPr component video source
- Standard in-wall outlets



Hardware Installation

1. Remove the 2 screws from the front face plate and remove the face plate.
2. Plug the RJ45 connector from the wall outlet to the back of the unit.
3. Mount and secure the unit into the wall outlet using the supplied screws.
4. Mount and secure the front face plate to the unit again.
5. Repeat steps 1-4 for the other unit.
6. Connect the component video/digital audio source to one unit and the component display/digital audio receiver to the other.

Distances and Resolutions

Distance	Maximum Resolution
50m/150ft	720p/1080i
100m/330ft	480p/480i

Specifications

Signal Type	Component video (yPbPr) S/PDIF digital audio
Connectors	3 x RCA component video 1 x RCA digital coax audio 1 x RJ45
Maximum Resolution	720p/1080i
Maximum Distance	100 meters
Power	Self-Powered
Colour	White
Material	Plastic
Weight	100g
Dimensions	115.0mm x 70.0mm x 61.0mm

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a one year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.