

40 Pin Female IDE to SATA Converter

IDE2SAT25

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com


IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

Introduction

Thank you for purchasing a StarTech.com IDE2SAT25 IDE to Single Port SATA Adapter. The IDE2SAT25 is a versatile solution, allowing you to use newer 2.5" or 3.5" SATA hard drives with older IDE-only motherboards. Its low profile size allows the adapter to plug directly into the motherboard, making it ideal for small form factor systems and preserving space within larger systems.



*actual product may vary from photos

Packaging Contents

- 1 x IDE to SATA Adapter
- 1 x Y Cable (LP4 to LP4 + SP4)
- 1 x SATA Cable
- 1 x Instruction Manual

Features

- Fully compatible with Ultra ATA 133 specifications
- Serial ATA 1.0 compliant

Installation

1. Connect the serial ATA cable and "Y" split cable to the IDE2SAT25.
2. Connect the Ultra ATA (40pin) to the Motherboard IDE connector.
3. Connect the other end of the Serial ATA cable to the Serial ATA device.
4. Connect the other end of "Y" split power cable to the power source.
5. Do not forget to connect a power cable to the hard disk.

Note: No driver is needed to install the IDE2SAT25. It only acts as a bridge adapter between the Serial ATA and Ultra ATA interfaces.

Specifications

Interface	IDE to SATA Host Bridge
Controller	JMicron JM20330
Bus	Parallel ATA Bus
No. of ports	1 port
Port Type	SATA
Driver Support	Windows 7, Windows Server 2008 R2/Server 2003/2000/XP/Vista, Linux
Regulatory Approvals	CE, FCC

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names & Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

Warranty Information

This product is backed by a lifetime warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.