



CN.1	Signal Assignment	CN.2	WIRE	
1	TMDS DaTa2+	1	WHITE	WHITE MYLAR
2	TMDS DaTa2 Shield	2	DRAIN	
3	TMDS DaTa2-	3	BLUE	
4	TMDS DaTa1+	4	WHITE	RED MYLAR
5	TMDS DaTa1 Shield	5	DRAIN	
6	TMDS DaTa1-	6	BLUE	
7	TMDS DaTa0+	7	WHITE	GREEN MYLAR
8	TMDS DaTa0 Shield	8	DRAIN	
9	TMDS DaTa0-	9	BLUE	
10	TMDS Clock+	10	WHITE	ORANGE MYLAR
11	TMDS Clock Shield	11	DRAIN	
12	TMDS Clock-	12	BLUE	
14	Utility/HEAC+	14	WHITE	WHITE MYLAR
17	DDC/CEC Ground/HEAC Shield	17	DRAIN	
19	Hot Plug Detect/HEAC-	19	YELLOW	
13	CEC	13	RED	
15	SCL	15	PURPLE	
16	SDA	16	BLUE	
18	+5V Power	18	GREEN	
SHELL		SHELL	BRAID	

Customer Part No.(F)	L:mm
HMMM20MA	20000±150
HDMIMM80AC	25000±200
HMMM30MA	30000±200

OVER MOLD:BLACK PVC	5
Module: HT7180-M-00	4
HDMI A TYPE 19PIN PLUG (GOLD PLATED CONTACTS & SHELL.)	3
HDMI A TYPE 19PIN PLUG WITH MODULE(GOLD PLATED CONTACTS & SHELL.)	2
HDMI CABLE [(24AWG*2+MMAEAM)*4+(26AWG*2+EAMM)*1+(32AWG*3+28AWG*1)] +AB BRAID:65% OD:8.5mm PVC BLACK	1
<b>MATERIALS LIST &amp; SPEC. DESCRIPTION</b>	<b>ITEM</b>

THIRD ANGLE PROJECTION

**GENERAL NOTES**  
DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

**StarTech.com**

PRODUCT ID	HMMMxxMA
DESCRIPTION	Active HDMI Cable - 4K High Speed HDMI Cable with Ethernet
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>
	<b>UPLOAD DATE: 4/08/2022</b>