


8 Port 10/100Mbps Industrial Power over Ethernet Network Switch


IES8100POE / IES8100POEGB / IES8100POEEU

- DE: Bedienungsanleitung - de.startech.com
- FR: Guide de l'utilisateur - fr.startech.com
- ES: Guía del usuario - es.startech.com
- IT: Guida per l'uso - it.startech.com
- NL: Gebruiksaanwijzing - nl.startech.com
- PT: Guia do usuário - pt.startech.com

Front View



Rear View




*actual product may vary from photos

Packaging Contents

- 1 x 8 Port PoE Network Switch
- 1 x Power Cord
- 1 x Instruction Manual

LEDs



System Requirements

- RJ45 terminated Ethernet cabling
- Available AC electrical outlet

LED	Status	Description
Power	On	The switch is powered on
	Off	The switch is powered off
PoE	On	Linked to a PoE device
	Off	Not linked to a PoE device
Link/ACT	On	Link detected on port
	Off	No link detected on port
	Flashing	Data is being transmitted on port

Specifications

Number of Ports	8
Link Speed	10/100Mbps
Standards	IEEE 802.3af, IEEE802.3 10BASE-T, IEEE802.3u 100BASE-TX/FX, IEEE802.3x
PoE Output	48V DC, 15.4W (per port)
LEDs	1 x Power 8 x PoE Act/Status 8 x Link/Act
Flow Control	Half-duplex back-pressure IEEE802.3x full-duplex flow control
Switching Architecture	Store-and-Forward
Auto MDIX	Yes
Onboard Memory	512Kb
Enclosure Material	Steel
Power Consumption	132W Max
Power Adapter	100 ~ 240V AC, 50 ~ 60Hz
Operating Temperature	0°C ~ 45°C (32°F ~ 113°F)
Storage Temperature	-10°C ~ 70°C (14°F ~ 158°F)
Humidity	10% ~ 95% RH
Dimensions (LxWxH)	160.0mm x 266.0mm x 44.0mm
Weight	1400g

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.