


Keyed Laptop Lock

Product Diagram (LTLOCKKEY)



	Components	Function
1	Key	<ul style="list-style-type: none">Used to lock the Keyed Laptop Lock.
2	Lock	<ul style="list-style-type: none">Used to lock and unlock the Lock from a Lock Slot.
3	Locking Hook	<ul style="list-style-type: none">Used to connect the Lock to a Lock Port.
4	Security Cable	<ul style="list-style-type: none">Used to secure a Device to a secure stationary object.


Requirements

For the latest requirements, please visit www.startech.com/LTLOCKKEY

Securing a Device

Using the Key

1. Wrap the **Security Cable** around a secure stationary object and pull the **Lock** through the loop on the **Security Cable**.



Security Cable

2. Insert the **Key** into the **Lock**. Push and turn the **Key** counter-clockwise until the lock mechanism engages the **Lock Slot** on a **Laptop**, **Docking Station**, or other compatible **Device**.

3. Remove the **Key** from the **Lock**.


Using the Push-to-Lock Function

Note: In order to use this function the lock must be in the unlocked state.

1. Insert the **Locking Hook** into a **Lock Slot** on the **Device**.
2. Push the **Lock** button (key hole) to engage the locking mechanism.

Unlocking a Device

1. Insert the **Key** into the **Lock**. Push and turn the **Key** clockwise to disengage the lock mechanism from the **Lock Slot**.
2. Gently pull the **Lock** out of the **Lock Slot**.
3. Turn the **Key** a quarter turn counter-clockwise and remove it from the **Lock**.



Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Warranty Information

This product is backed by a two-year warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Safety Measures

- If product has an exposed circuit board, do not touch the product under power.

Mesures de sécurité

- Si l'un des circuits imprimés du produit est visible, ne pas touchez le produit lorsqu'il est sous tension.

安全対策

- 製品に露出した状態の回路基盤が含まれる場合、電源が入っている状態で製品に触らないでください。

Misure di sicurezza

- Se il prodotto ha un circuito stampato visibile, non toccare il prodotto quando è acceso.

Säkerhetsåtgärder

- Rör aldrig vid enheter med oskyddade kretskort när strömmen är påslagen.

StarTech.com Ltd. **StarTech.com LLP** **StarTech.com Ltd.** FR: fr.startech.com
45 Artisans Cres 2500 Creekside Unit B, Pinnacle 15 DE: de.startech.com
London, Ontario Parkway Gowerton Rd, ES: es.startech.com
N5V 5E9 Lockbourne, Ohio Brackmills NL: nl.startech.com
Canada 43137 Northampton IT: it.startech.com
U.S.A. NN4 7BW JP: jp.startech.com
United Kingdom