

4 Bay 1U Rackmount 3.5" SATA HDD Enclosure

SAT35401U



*actual product may vary from photos

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols


This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents


Product Diagram	1
Front View	1
Rear View	1
Introduction	2
Packaging Contents	2
System Requirements.....	2
Hardware Installation	3
Hard Drive Removal Steps	4
Rack Mounting Instructions	5
Power Adapter Bracket Installation (optional)	5
Technical Support	6
Warranty Information.....	6

Product Diagram

Front View



Rear View



Introduction

Packaging Contents

- 1 x 4 bay rackmount 3.5" HDD enclosure
- 1 x mounting bracket set
- 1 x universal power adapter (NA/JP, EU, UK, ANZ)
- 1 x hole cover set
- 1 x rubber feet set
- 1 x power adapter bracket with mounting hardware
- 1 x instruction manual


System Requirements

- Computer System
- SAS/eSATA Host controller
- Mini SAS cable


WARNING! Hard drives and storage enclosures require careful handling, especially when being transported. If you are not careful with your hard disk, lost data may result. Always handle your hard drive and storage device with caution. Be sure that you are properly grounded by wearing an anti-static strap when handling computer components or discharge yourself of any static electricity build-up by touching a large grounded metal surface (such as the computer case) for several seconds.

Hardware Installation


1. Open the Drive Door on the front of the enclosure, by inserting the provided key, into the key hole, and turning clockwise. The door will swing open outward.



2. Slide up to four drives into the available HDD installation bays.




3. Close the drive door by swinging it up, and lock it closed by inserting the provided




key and turning it counter clockwise.

4. Connect the mini SAS cable (not included) from the External Mini SAS port on the SAT35401U, to your SAS/SATA Host controller.
5. Connect the included power adapter from the Power Adapter port on the SAT35401U to an available AC Power outlet.




Hard Drive Removal Steps

1. Open the Drive Door on the front of the enclosure, by inserting the Provided key, into the key hole, and turning clockwise. The door will swing open outward.



2. Pull open the HDD removal lever, the drive will slide outward.




3. Remove Hard Drive.

Rack Mounting Instructions

1. Install Mounting hardware by fixing the included mounting brackets using the provided screws to either side of the SAT35401U.
2. Consult the manual included with your Rack for Rack installation steps.

Power Adapter Bracket Installation (optional)

1. Facing the front of the unit, hold the included Power adapter bracket into place lining up the mounting holes on the bracket with the installation holes on the .
2. Using a screw driver (not included) fix 2 mounting screws into the SAT3401U, through the power adapter bracket holding it into place.



3. The power adapter can now be hung on the bracket when the enclosure is mounted.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.