

0.3 m Round Latching SATA Cable

Product Diagram (SATRD30CM)



Part		Function		
1	Latching SATA Connectors	 Connect a SATA Drive to a Computer SATA 7 pin - data only 		
2	Latch	Prevents disconnections		
3	SATA Cable	 Color - black Length - 0.3 m Wire Gauge - 30 AWG Compliant with SATA 6Gb/s specifications 		

Requirements

For the latest requirements please visit: <u>www.startech.com/SATRD30CM</u>.

- SATA Drive
- Computer

Installation

• Connect the Latching SATA Connectors to the SATA Port on a SATA Drive and to an available SATA Port on a Computer's Motherboard.

Operation

Disconnecting the Latching SATA Connectors

- Press and Hold the Latch on the Latching SATA Connectors and Pull gently.
 - **Note:** If you encounter resistance when attempting to remove the **Latching SATA Connectors**, reposition your finger over the **Latch** and try again.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of thirdparty companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Warranty Information

This product is backed by a lifetime warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Safety Measures

• If product has an exposed circuit board, do not touch the product under power.

Mesures de sécurité

• Si l'un des circuits imprimés du produit est visible, ne pas touchez le produit lorsqu'il est sous tension.

安全対策

製品に露出した状態の回路基盤が含まれる場合、電源が入っている状態で製品に触らないでください。

Misure di sicurezza

• Se il prodotto ha un circuito stampato visibile, non toccare il prodotto guando è acceso.

Säkerhetsåtgärder

Rör aldrig vid enheter med oskyddade kretskort när strömmen är påslagen.

StarTech.com Ltd. 45 Artisans Cres London, Ontario NSV 5E9 Canada	StarTech.com LLP 2500 Creekside Parkwy Lockbourne, Ohio 43137 U.S.A.	StarTech.com Ltd. Unit B, Pinnacle 15 Gowerton Rd, Brackmills Northampton NN4 7BW United Kingdom	FR: fr.startech.com DE: de.startech.com ES: es.startech.com NL: nl.startech.com IT: it.startech.com JP: jp.startech.com
--	---	--	--