

2.5" Hot Swap Hard Drive Tray

SATSASTRX25



*actual product may vary from photos

FR: Guide de l'utilisateur - fr.startech.com
DE: Bedienungsanleitung - de.startech.com
ES: Guía del usuario - es.startech.com
NL: Gebruiksaanwijzing - nl.startech.com
PT: Guia do usuário - pt.startech.com
IT: Guida per l'uso - it.startech.com

For the latest information, technical specifications, and support for this product, please visit www.startech.com/SATSASTRX25.

Table of Contents

Introduction	1
Packaging contents	1
System requirements	1
Product diagram	2
Install a drive	3
Remove a drive	3
Additional information	3
Technical support	4
Warranty information	4

Introduction

The SATSASTRX25 provides a convenient and fast way to hot swap drives with the StarTech.com [single-bay backplane](#) and the [four-bay backplane](#). This means that you can exchange the drives while the backplanes are still running.

You can use the SATSASTRX25 as an extra tray to create expandable storage or as part of a rotating backup solution. The drive tray supports both SAS and SATA 2.5 in. drives, ranging in height from 5 to 15 mm. To maximize the performance of your drives, the single and four-bay backplanes support SAS II and SATA III, enabling file transfer speeds up to 6Gbps when paired with a compatible controller.

Packaging contents

- 1 x 2.5 in. hot-swap drive tray
- 4 x screws
- 2 x keys

System requirements

- 2.5 in. SAS or SATA drive
- A screwdriver
- Supported drive heights include 5 mm, 7 mm, 9.5 mm, 12.5 mm, and 15 mm
- Designed to be used with StarTech.com products [SATSASBP125](#) and [SATSASBP425](#)

The SATSASTRX25 is OS independent and doesn't require any additional drivers or software.

System requirements are subject to change. For the latest requirements, please visit www.startech.com/SATSASTRX25.

Product diagram



The SATSASTRX25 is designed to be used with the StarTech.com [SATSASBP125](#) and [SATSASBP425](#) series of backplanes.



Install a drive

The SATSASTRX25 supports drives that are 5 mm, 7 mm, 9.5 mm, 12.5 mm, or 15 mm high.

Warning! Drives should be handled carefully, especially when they're transported. If you're not careful with your drives, you may lose data as a result. Always handle storage devices with caution. Make sure that you're properly grounded by wearing an anti-static strap when you install any computer component. If an anti-static strap isn't available, touch a large grounded metal surface for several seconds to discharge any built-up static electricity.

1. Insert the drive into the drive tray, making sure that the mounting holes on the bottom of the drive line up with the mounting holes on the drive tray.
2. Insert the provided screws through the mounting holes in the drive tray and into the holes in the drive.
3. Tighten the screws by turning them clockwise.

Remove a drive

Warning! You should disconnect the drive from your computer before you physically remove the drive tray from the backplane.

1. Remove the drive tray from the SATSASBPx25 backplane.
2. Remove the screws from the mounting holes in the drive tray and the drive.
3. Remove the drive from the drive tray.

Additional information

If you require more information about how to use the drive tray or the backplane that the tray goes into, see the documentation that came with the [SATSASBP125](#) or [SATSASBP425](#) backplane.

Technical support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty information

This product is backed by a two-year warranty.

StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.