

USB 3.0 Capture Device for DVI Video

USB32DVCAPRO



*actual product may vary from photos

FR: Guide de l'utilisateur - fr.startech.com

DE: Bedienungsanleitung - de.startech.com

ES: Guía del usuario - es.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

IT: Guida per l'uso - it.startech.com

For the latest information, technical specifications, and support for this product, please visit www.StarTech.com/USB32DVCAPRO

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

Product diagram	1
Front view	1
Rear view	1
Introduction	2
Packaging contents	2
System requirements	2
Software installation	3
Driver installation for Windows computers	3
Hardware installation	3
Warranty information	4

Product diagram

Front view



Rear view



Introduction

Packaging contents

- 1 x USB 3.0 capture device for DVI video
- 1 x USB 3.0 cable
- 1 x Manual

System requirements

- 1 x DVI video source with cabling
- 1 x DVI display with cabling (optional for video passthrough)
- 1 x computer system with minimum:
 - CPU Intel® Core™ i3
 - Memory: 4 GB
 - Video: 1024×768, DirectX® 9.0c compatible graphics card
 - Operating system: Windows® 10 (32/64), 8 / 8.1 (32/64bit), 7 (32/64bit)
- Operating system requirements are subject to change. For the latest requirements, please visit www.StarTech.com/USB32DVAPRO

Software installation



To use the video adapter in USB mode, ensure the software installation steps have been completed **before you connect the adapter to your computer.**

Driver installation for Windows computers

Note: you will need to restart your computer during the software installation process. Please be sure to save any unsaved material before you install the software.

1. Download the latest software from the StarTech.com website:
<http://www.StarTech.com/USB32DVCAPRO>
2. The software will be compressed in a .zip folder. Extract the contents of the folder to a location on your computer that's easy to access, such as your **Desktop** or **Downloads** folder.
3. Once the files have been extracted, open the **Windows** folder, and launch the **Setup(.exe)** file. This installer file will install the capture device drivers.
4. Follow the on-screen prompts to complete the installation, and when instructed to do so, restart your computer.

Hardware installation

1. Connect a DVI cable (sold separately) to the output port on your video source device and to the video adapter's **DVI In** port.
2. Connect the included USB cable to the video adapter's **USB** port, and to a USB port on your computer system.
3. Your computer will automatically detect the USB drivers for the video adapter and install them.
4. To preview the video source that's being sent through the capture device, by connecting a DVI cable (not included) to the video adapter's **DVI Out** port and to a DVI display.

Warranty information

This product is backed by a two-year warranty.

StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.

Reviews

Share your experiences using StarTech.com products, including product applications and setup, what you love about the products, and areas for improvement.

StarTech.com Ltd.	StarTech.com LLP	StarTech.com Ltd.	StarTech.com Ltd.
45 Artisans Crescent	4490 South Hamilton Road	Unit B, Pinnacle 15 Gowerton Road Brackmills,	Siriusdreef 17-27 2132 WT Hoofddorp
London, Ontario N5V 5E9 Canada	Groveport, Ohio 43125 U.S.A.	Northampton NN4 7BW United Kingdom	The Netherlands

FR: fr.startech.com

ES: es.startech.com

IT: it.startech.com

DE: de.startech.com

NL: nl.startech.com

JP: jp.startech.com