

3.5in Black Multi Port Panel for Front Drive Bay with eSATA

35BAYPANELBK

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com


IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

Packaging Contents

- 3.5" Front Panel
- SATA Cable
- 6-pin FireWire to Header Cable
- USB Header Cable
- Audio Header Cable
- Screw Kit
- Instruction Manual



*actual product may vary from photos

- | | |
|---|--|
| 1 | 15-pin Header - Internal IEEE 1394
Firewire and Audio Cable |
| 2 | eSATA - to SATA connection |
| 3 | 2x 9-pin USB Header |


Installation

To prepare for installation, connect the appropriate cables to the USB1, USB2, eSATA, 1394 (FireWire), MIC (Microphone) and SPK (Speaker) ports on the Multiport Panel, as shown:

1. Make sure that your PC is turned off.
2. Remove the PC Case Cover. Similarly, remove a 3.5" bay cover from the front panel of the Computer Case.
3. Pass the cables (connected to the Bay Panel as shown above) through the open bay, allowing access to the remaining ends from within the case.
4. With the cables now accessible from within the case, insert the Multiport Panel into the open bay and secure it using the small screws provided.
5. Connect the remaining ends of the cables to the necessary ports on the motherboard. For the specific location of each connector as it pertains to the host motherboard, please consult the documentation that accompanied your motherboard or computer at the time of purchase.

Please note: If the motherboard does not have an available (9-pin) FireWire header connection, please connect the IEEE 1394 external cable (included, shown below) to the IEEE 1394 connector on the internal 1394 FireWire/Audio cable (shown as 1 in diagram), then insert the FireWire connector provided by the IEEE 1394 external cable into an available external FireWire port on the computer.

IEEE 1394 External Cable



Specifications

Connector Types	1x SATA plug 1x FireWire 6 pin Female 2x USB A Female 9 pin 1x Audio Female Connector
Regulatory Certifications	CE, RoHS, FCC
Dimensions	102mm (4.02in) x 25mm (0.98in) x 121mm (4.77in)
Weight	250g (8.8oz)

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.