

DVI EDID Emulator

DVIEDIDDET



*actual product may vary from photos

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

Introduction	1
Packaging Contents	1
System Requirements.....	1
Installation	2
Software Installation.....	3
Configuration Diagram	4
Operation	5
Front Panel Pushbuttons	5
Keyboard Hotkeys.....	5
KVM Switcher Software.....	6
Specifications	9
Technical Support	10
Warranty Information	10

Introduction

The DVIEDIDDET DVI EDID Emulator captures and retains EDID information from a monitor/display and can then be connected to the video signal source, emulating the information in order to trick the video source (video card) into outputting the same video signal - even if the display is not directly connected to the video source or is connected using a video extension system.

Since most video extender systems don't offer EDID communication between the signal source and a remote display, the DVI EDID Emulator (DVIEDIDDET) is a perfect workaround for ensuring the optimum signal is provided to the display, regardless of whether or not there is a direct connection between the source and the display.


Features

- Make your computer operate as though it is directly connected to the display, even while using converters or Cat5 extenders
- Stores EDID settings even when unit has been unplugged

Package Contents


- 1 X EDID Detector / Capture Box
- 1 X Instruction Manual
- 1 X Power Adapter

Front View



1. DVI In
2. Power Jack

Rear View



1. Power LED
2. DVI Out


Installation

1. Power on the monitor being used, and connect it to the DVI Out on the DD-01 using the DVI cable.
2. Plug the 5V power supply into the DD-01.
3. Unplug the 5V power supply and monitor cable from the DD-01.
4. Connect the PC to the DVI In of the DD-01 using the DVI cable.
5. Power on the PC.

Specifications

Input Connector	1 DVI Female
Output Connector	1 DVI Female
Max. Resolution	1600x1200
Cable Distance	10 m (Max.)
Power Adapter (Min.)	DC 5V 1.0A
Housing	Metal
Weight	138 g
Dimensions (LxWxH)	67x56x38 mm

Pin Configuration



Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.