

## Replacement Fan Kit for DRW115 Series Mobile Racks

DRW115FANKIT

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com



PT: Guia do usuário - pt.startech.com

\*actual product may vary from photos

### Specifications


<b>Warranty</b>	1 Year warranty
<b>Color</b>	Black
<b>Product Height</b>	1.57 in [40 mm]
<b>Input Current</b>	0.05
<b>Product Length</b>	1.57 in [40 mm]
<b>Output Voltage</b>	12 DC
<b>Carton Quantity</b>	200
<b>Shipping (Package) Weight</b>	0.08 lb [0.04 kg]
<b>Product Weight</b>	0.95 oz [27 g]
<b>Product Width</b>	0.41 in [10.4 mm]
<b>General Specifications</b>	Kit includes two 40 x 40 x 10mm fans 4500 RPM +/- 10% Max AirFlow 2.71 CFM
<b>Noise Level</b>	< 19 dBa
<b>MTBF</b>	40,000 hours @ 25 degrees C
<b>Input Power Consumption</b>	0.6 W





1. Remove the caddy from the bay by lifting the handle and sliding the caddy out of the bay.


2. Remove each of the two screws situated on the sides of the caddy.




5. Disconnect the fans from the power cable(s).




6. Unscrew the fans from the bracket, noting the placement of the screws and the available screw holes.



3. Remove the top panel from the caddy by pressing the cover release button and sliding the lid towards the back of the caddy.



4. Remove the installed drive (if necessary), then remove the fan bracket (with fans attached) from the caddy.



7. Remove the fans from the bracket.

8. Once the original fans have been removed, attach the replacement fans to the bracket, positioning the power cables to the space left between the fans. (see illustrations, step #4, #6).



9. Fasten the fans to the bracket using the screws removed in step #3, and connect the power cables from the fans to the main (caddy) power cable.

10. Replace the fan bracket (with new fans attached) into the caddy.  
 11. With the replacement fans in place, re-install the hard drive in the caddy then replace the top panel (removed in step #3).  
 12. Re-fasten the screws removed in step #2.  
 13. With the handle lifted, slide the caddy into the bay until it is firmly seated. Lower the handle to click the caddy into its proper position.

## FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

## Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

## Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit [www.startech.com/downloads](http://www.startech.com/downloads)

## Warranty Information

This product is backed by a one year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

## Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.