

eSATA/USB 2.0 to 2.5/3.5in SATA HDD Dock

SATDOCKCRH/GB



DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

Reorient or relocate the receiving antenna.

Increase the separation between the equipment and receiver.

Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

Introduction.....	1
Packaging Contents	1
System Requirements	1
Front View	2
Rear View	2
Installation.....	3
Hardware Installation.....	3
Driver Installation	3
Specifications	4
Technical Support.....	5
Warranty Information.....	5

Introduction

The SATDOCKCRH combines the convenience of a SATA docking station with a 13-in-1 card reader and 2-port USB hub, and can be connected to a host computer through either USB or eSATA.

Providing immediate access to SATA hard drive contents, (by simply inserting the HDD into the SATA dock), SATDOCKCRH lets you copy the contents between your memory cards, flash drives and bare SATA hard drives all from one centrally connected device when connected to a computer. The HDD docking station supports data transfer speeds of up to 3 Gbps (using eSATA) and 480Mbps (using USB 2.0) between host and dock - ensuring effortless data dumps, backups and hassle-free file transfers.


Packaging Contents

- 1 x SATDOCKCRH hard drive dock
- 1 x eSATA cable
- 1 x USB cable (A-B)
- 1 x Power Adapter
- 1 x Instruction Manual


System Requirements

- USB and/or eSATA enabled computer system
- Windows 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and MAC OS X and up

Front View



Rear View



Installation

WARNING: Hard drives require careful handling, especially when being transported. If you are not careful with your hard disk, lost data may result. Always handle storage devices with caution.

Hardware Installation

1. Connect the external power adapter from the hard drive dock to a power outlet.
2. Insert a 2.5" or 3.5" hard drive into the top loading slot. Make sure that the connectors on the hard drive are facing the same corner of the slot that has a cutout in the door. The label on the hard drive should face the front of the hard drive dock.
3. Connect the USB cable and eSATA cable from the hard drive dock to the computer system.

NOTE: The hard drive dock can be used with only the USB connection, if eSATA is not available on the computer system. The hard drive can be used over eSATA alone, however to use the USB hub and/or card reader, the USB must be connected.

4. Once all connections are made, press the power button on the top of the hard drive dock.
5. To remove the hard drive, make sure it is currently not being accessed by the computer then unmount or uninstall the disk drive from the operating system (see documentation for your operating system). Press the drive ejection button on the top of the hard drive dock to release the drive. Then pull the drive from the slot.

Driver Installation

Windows 2000/XP/Vista/7, Mac OS X, Linux

No driver installation is required for these operating systems, as the hard drive dock, USB hub and card reader are natively supported, so the drivers are already installed.

Specifications

Bus Interface	USB 2.0 SATA 3.0Gb/s
Connectors	1 x USB type B 1 x eSATA 2 x USB type A 1 x SD/MMC/MS card slot
LEDs	1 x Power/Activity
Hard Drive Compatibility	2.5" or 3.5" SATA 1.5/3.0 Gb/s
Flash Card Compatibility	<ul style="list-style-type: none">• MS/MS Pro• SD/MMC• MS Duo, MS Pro Duo, MS Pro-HG Duo• RS-MMC• SDHC• MS Micro• Mini-SD, Micro-SD• Micro-SDHC
Maximum Data Transfer Rate	USB: 480 Mb/s SATA: 3 Gb/s
Power Adapter	12VDC, 2.5A, center positive
Dimensions	145.0mm x 93.0mm x 65.0mm
Weight	413g
Compatible Operating Systems	Windows 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and MAC OS X and up

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/ support and access our comprehensive selection of online tools, documentation, and downloads.

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.



Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.