




(A).Wire Pin Assignment and Wire Description.


CN.1	PAIR#	CN.2	COLOR	
1		12	BLUE	red mylar
3		10	WHITE	
2		11	DRAIN	
4		9	BLUE	yellow mylar
6		7	WHITE	
5		8	DRAIN	
7		6	BLUE	orange mylar
9		4	WHITE	
8		5	DRAIN	
10		3	BLUE	blue mylar
12		1	WHITE	
11		2	DRAIN	
13	SIGNAL	13	GREEN	
14	SIGNAL	14	RED	
15		15	BLUE	green mylar
17		17	WHITE	
16		16	DRAIN	
18	SIGNAL	18	PURPLE	
19	SIGNAL	19	BLUE	
SHELL		SHELL	BRAID	

(B). Electrical Testing :

- a. OPEN/SHORT:100% Testing Line-Process.
- b. HI-POT: 100V AC/0.1sec.
- c. INSULATION RESISTANCE:10MΩ(MIN) 100V DC
- d. CONDUCTION RESISTANCE:5Ω(MAX)

④	MOLDING:PVC BLACK	/
③	DISPLAYPORT TOP/LOWER CASING:PC BLACK	1
②	DISPLAYPORT 20PIN PLUG,TERMINAL Au-PLATED SHELL Au-PLATED	1
①	DP CABLE [(28AWGx2C+MMEAM)x5P+28AWGx4C]+AB OD:7.5 Braid:85% BLACK PVC	/
ITEM	MATERIALS LIST & SPEC. DESCRIPTION	Q'TY

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	DP14MM4M		
DESCRIPTION	4M DISPLAYPORT 1.4 CABLE		
REV: A	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 03/16/2020