




1m and 2m HDMI Cable (HDMI Premium Certified)


HDMMXXMP



CONNECTION



Part No.	Length (L)
HDMM1MP	1000±30mm
HDMM2MP	2000±50mm



Marking:PREMIUM HIGH SPEED HDMI R(logo) CABLE WITH ETHERNET UL(Logo) AWM 20276 VW-1 80°C 30V E81280-D CHING TAI

ELECTRIC TESTING:

- 1.100% OPEN & SHORT TESTING
- 2. INSULATION RESISTANCE: $\geq 20 \text{ M}\Omega$
- 3. CONDUCTOR RESISTANCE: $\leq 3 \Omega$
- 4. VOLTAGE: 300V DC/0.1S

3	{[(1/0.254Bc+HDPE)*1P+1/0.254Tc+AL/Mylar]*5P+(1/0.254Bc+HDPE)*4C+Filler+AL Mylar+16/13/0.08(85%)Tc Braid}*1C OD=6.0±0.15MM Jacket=Black PVC Jacket with White Text :PREMIUM HIGH SPEED HDMI R(logo) CABLE WITH ETHERNET UL(Logo) AWM 20276 VW-1 80°C 30V E81280-D CHING TAI (307B87U01800000)
2	PVC - Black 60P (31401012060/CYT-YT-3342/-0905-*/3278)
1	HDMI Plug - Gold Plated (3033700AP003/3033700AVG05/3033700APN04)
ITEM	SPECIFICATION