

## 3.5in Silver USB 2.0 to SATA External Hard Drive Enclosure

SAT3510U2V / SAT3510U2VGB / SAT3510U2VEU  
SAT3510BU2V / SAT3510BUVGB / SAT3510BUVEU



\*actual product may vary from photos

DE: Bedienungsanleitung - [de.startech.com](http://de.startech.com)

FR: Guide de l'utilisateur - [fr.startech.com](http://fr.startech.com)

ES: Guía del usuario - [es.startech.com](http://es.startech.com)

IT: Guida per l'uso - [it.startech.com](http://it.startech.com)

NL: Gebruiksaanwijzing - [nl.startech.com](http://nl.startech.com)

PT: Guia do usuário - [pt.startech.com](http://pt.startech.com)

For the most up-to-date information, please visit: [www.startech.com](http://www.startech.com)

## FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

## Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

# Table of Contents

<b>Introduction</b> .....	<b>1</b>
Packaging Contents .....	1
System Requirements.....	1
<b>Hardware Guide</b> .....	<b>2</b>
Front Panel View .....	2
Rear Panel View.....	2
<b>Installation</b> .....	<b>3</b>
Hardware Installation .....	3
Driver Installation.....	6
<b>Specifications</b> .....	<b>7</b>
<b>Technical Support</b> .....	<b>8</b>
<b>Warranty Information</b> .....	<b>8</b>

# Introduction

Thank you for purchasing a StarTech.com SAT3510U2V / SAT3510BU2V InfoSafe 3.5" USB 2.0 SATA Aluminum Hard Drive Enclosure. This cost-effective storage solution suits a wide variety of applications including file and application sharing between desktop and notebook computers, data archiving, or simply backing up existing hard drives to preserve data security.

## Packaging Contents

- 1 x Aluminum HDD Enclosure
- 1 x USB (A-B) Cable
- 1 x Screw Kit
- 1 x Plastic Stand
- 1x Power Adapter
- 1 x Instruction Manual

## System Requirements

- 3.5" SATA hard drive
- An available (nearby) power outlet
- A host PC or Mac computer system with an available USB port
- Mac OS 9.0 and up, and Linux

# Hardware Guide

## Front Panel View

Power/Activity LED



Power/Activity LED

## Screw Kit



## Power Adapter



## USB A-B Cable



## Rear Panel View

Power Adapter Port

On/Off Switch

USB type B Port



## Plastic Stand



# Installation




**WARNING!** Hard drives and storage enclosures require careful handling, especially when being transported. If you are not careful with your hard disk, lost data may result. Always handle your hard drive and storage device with caution. Be sure that you are properly grounded by wearing an anti-static strap when handling computer components or discharge yourself of any static electricity build-up by touching a large grounded metal surface (such as the computer case) for several seconds.

## Hardware Installation


1. Remove the Rear Panel, to expose the internal SATA connections:




2. Position the hard drive you wish to install such that the SATA connection is facing towards the SATA interface connector provided by the Enclosure's front panel:




3. With the hard drive connected to the front panel, turn the drive over to expose its base. Fasten the hard drive to the front panel rails on both sides, using the screws provided (2):



4. Fasten the front panel (with drive attached) to the body of the Enclosure; be cautious that the drive and front panel are properly aligned with the body of the Enclosure, to prevent damage to the LEDs.



5. Fasten both sides of the case to lock the hard drive in place:



6. Fasten the rear panel to the Drive Enclosure on both sides using the screws (2) provided.





7. Once the drive has been secured within the Enclosure, connect the DC 12V power adapter to the power adapter port. Connect the remaining end of the power adapter to an available power outlet.
8. Connect the USB A-B cable to the USB B port on the rear panel of the Enclosure, then connect the remaining end of the cable to the host computer.
9. With the host computer powered on, power on the Drive Enclosure using the On/Off switch. The operating system will detect the presence of the added drive, following which you will be able to properly format/partition the installed drive from within the operating system.

## Driver Installation

No driver installation is required for the supported operating systems, as this enclosure is natively supported, so the drivers are already installed.

# Specifications

<b>Bus Type</b>	USB 2.0
<b>Chipset</b>	SunPlus SPIF301
<b>Maximum Data Transfer Rate</b>	480 Mbps
<b>LED Indicators</b>	Solid Green -Power status Blinking Green - Read/Write Drive Activity
<b>Enclosure Casing Material</b>	Aluminum
<b>Power Adapter</b>	12V DC, 2000mA
<b>Dimensions (L x W x H)</b>	193 mm x 113 mm x 31 mm (7.6" x 4.45" x 1.22")
<b>Weight</b>	325 g (11.47 oz)
<b>OS Compatibility</b>	Mac OS 9.0 and up, and Linux, Windows 2000 / Windows 2003 / Windows 7 / Windows 98SE / Windows ME / Windows XP

# Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit [www.startech.com/downloads](http://www.startech.com/downloads)

## Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

### Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit [www.startech.com](http://www.startech.com) for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

*StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.*