

Two Way Digital Coax to Toslink Audio Converter Repeater

SPDIFCOAXTOS



*actual product may vary from photos

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

Introduction	1
Features	1
Package Contents	1
Operating Controls and Functions	2
Input Panel	2
Output Panel.....	2
Switcher Panel.....	3
Installation	3
Specifications.....	4
Technical Support	5
Warranty Information.....	5

Introduction

Thank you for purchasing a StarTech.com Two-Way Digital Audio Converter / Repeater. This innovative device allows you to convert and/or extend your Toslink or Digital Coaxial audio input, without sacrificing any signal quality, and offers simplified switching between the Toslink or Digital Coax signal inputs using a built-on mini-switch - ensuring a convenient and top quality audio experience.

Features


- Supports two way audio conversion: Toslink to digital coaxial or vice versa
- Supports amplification of S/PDIF audio signals and extends their transferring distance, through coaxial and/or Toslink cables.
- Input 2 to 5.1 channel audio. Output channels will always be the same as audio input channels
- Compact design saves space
- Easy installation

Package Contents

- 1 x User manual
- 1 x SPDIFCOAXTOS Audio Converter
- 1 x Power Adapter

Operating Controls and Functions

Input Panel




1. Coaxial Input

Connect to the **output** port of your S/PDIF audio source (e.g. DVD player, amplifier) using Coaxial cable.

2. Toslink Input

Connect to the **output** port of your S/PDIF audio source, (e.g. DVD player, amplifier) using Toslink cable

Output Panel




1. Toslink Output:

Connect to the **input** port of your S/PDIF audio equipment such as an amplifier, using Toslink (optical fiber) cable.

2. Coaxial Output:

Connect to the **output** port of your S/PDIF audio equipment such as an amplifier, using Coaxial cable.

Switcher Panel




1. Input Selection

Use this switch to select which input to use - Toslink or Coaxial.

2. Power

Connect the power supply to the SPDIFCOAXTOS unit and connect the adapter to an electrical outlet.

Installation



Specifications

Input	1x Coaxial RCA port, 1x Toslink (Optical Fiber) port
Output	1x Coaxial RCA port, 1x Toslink (Optical Fiber)
Power	DC 5V
Dimension	42(W) x 40.5(D) x 22(H)mm
Weight	25g (Adapter not included)

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.