



NOTES:  
 1. 100% OPEN & SHORTS AND MISS WIRE TEST.  
 a. CONTACT RESISTANCE: 5 OHM MAX.  
 b. INSULATION RESISTANCE: 5M OHM MIN.  
 c. HI-POT: DC300V/0.01S.  
 2. ALL MATERIALS SHALL COMPLY WITH ROHS.

⑬	HEAT SHRINK TUBE: $\phi$ 3.0*7mm/1PC, $\phi$ 2.0*7mm/4PCS, $\phi$ 1.5*7mm/1PC, $\phi$ 1.0*7mm/4PCS
⑫	PE BAG: 300*130mm04,
⑪	CABLE TIE: L=170MM, BLACK PE
⑩	MOLDED THUMBSCREW #4-40, NICKEL PLATED, LENGTH: 46.4MM, COLOR: BLUE
⑨	MOLDED THUMBSCREW #4-40, NICKEL PLATED, LENGTH: 46.4MM, COLOR: GRAY
⑧	OUTER MOLDED: 50P PVC COLOR: BLACK
⑦	OUTER MOLDED: 50P PVC COLOR: BLUE
⑥	OUTER MOLDED: 60P PVC COLOR: GRAY
⑤	INNER MODEL: TRANSPARENT LDPE
④	USB A/M, SHELL: NICKEL PLATING, INSULATED: BLACK, TERMINAL: G/F
③	HDB: 15P/M, INSULATION: BLUE, SHELL: NICKEL PLATED
②	CABLE: UL2725 28AWG*1P+28AWG*2C+ADB, OD: 4.0MM, JACKET: GRAY PVC
①	CABLE: UL20276 (30AWG*1C+EAM)*3C+(30AWG*1C+EAM)*2C+(28AWG*1P+AM)*1C+28AWG*2C+30AWG*2C+AB, OD: 7.0MM, JACKET: GRAY PVC
PART	DESCRIPTION

THIRD ANGLE PROJECTION

**StarTech.com**

GENERAL NOTES		PRODUCT ID	SVUSBVGA6
DIMENSIONS ARE IN MM - DO NOT SCALE		DESCRIPTION	6 ft Ultra-Thin USB VGA 2-in-1 KVM Cable
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM		DO NOT SCALE	SHEET: 1 OF: 1
		UPLOAD DATE: 5/07/2026	