



PIN ASSIGNMENT

P1	WIRE TYPE	P2	COLOR
1		1	RED
2		2	WHITE
3		3	GREEN
4		4	BLACK
SHELL		SHELL	DRAIN

SKU	LENGTH
USBEXTAA3BK	915MM±25MM
USBEXTAA6BK	1830MM±30MM
USBEXTAA10BK	3000MM±40MM

NO.	NAME	MATERIAL DESCRIPTION	Q'TY	UNITS
5	INNER MOLD	LD-PE	A/R	KG
4	OVER MOLD	PVC , COLOR:BLACK	A/R	KG
3	CONNECTOR	USB A/F 4PIN (180° SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.	2	PCS
2	CONNECTOR	USB A/M (SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.	2	SET
1	CABLE	USB 2.0 UL2725 28#*1P+24#*2C+AL +D+B(16*4/0.12AL-M) OD:4.5mm BLACK PVC JACKET	A/R	M

THIRD ANGLE PROJECTION

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USBEXTAAxBK
DESCRIPTION	Black USB 2.0 Extension Cable A to A - M/F
DO NOT SCALE	SHEET: 1 OF: 1
UPLOAD DATE: 12/08/2021	