

Composite and S-Video to HDMI Video Converter

Product Diagrams (VID2HDCON2)

Front View



Rear View



Component		Function
1	Power LED Indicator	 Solid Red: The Universal Power Adapter is connected and the On/Off Switch is in the On position
2	Composite Video LED Indicator	 Solid Red: The Universal Power Adapter is connected, the On/Off Switch is in the On position, and the Composite Video Input Port is selected
3	S-Video LED Indicator	 Solid Red: The Universal Power Adapter is connected, the On/Off Switch is in the On position, and the S-Video Input Port is selected
4	Video Input Selection Button	Select the Source Device Video Signal

5	On/Off Switch	 The "O" icon indicates the Off position The "I" icon indicates the On position Toggle the On/Off Switch to power the Video Converter On or Off
6	DC/5V Power Input Port	 Connect a Power Source using the Universal Power Adapter
7	HDMI Output Port	Connect an HDMI Display Device
8	S-Video Input Port	Connect an S-Video Source Device
9	Composite Video Input Port	Connect a Composite Video Source Device
10	Right RCA Audio Input Port	 Connect an Audio Source to the Right Audio Channel
11	Left RCA Audio Input Port	Connect an Audio Source to the Left Audio Channel

Requirements

For the latest requirements, please visit www.startech.com/VID2HDCON2.

- Composite Video or S-Video Source Device x 1
- Composite Video or S-Video Cable x 1
- Audio Source x 1
- RCA Audio Cable x 1
- HDMI Display Device x 1
- HDMI Cable x 1
- Power Source x 1

Installation and Operation

- 1. Ensure all of the **Devices** are powered **Off**.
- 2. Connect a Composite Video Cable to the Composite Video Input Port on the Video Converter and to a Composite Video Source Device.

Or

Connect an **S-Video Cable** to the **S-Video Input Port** on the **Video Converter** and to an **S-Video Source Device**.

3. Connect the Right (Red) and Left (White) RCA Audio Cable Connectors to the Right and Left RCA Audio Input Ports on the Video Converter and to an Audio Source.

Note: Ensure the colors of the **Connectors** and **Ports** match.

- 4. Connect an **HDMI Cable** to the **HDMI Output Port** on the **Video Converter** and to an **HDMI Display Device**.
- 5. Connect the Universal Power Adapter to the DC/5V Power Port on the Video **Converter** and to an available **Power Source**.
- 6. Toggle the **On/Off Switch** to the **On** position.
- 7. Press and Release the Video Input Selection Button to match your Source Device (Composite or S-Video Device) video signal type.

Universal Power Adapter - Power Clips

The Universal Power Adapter comes with 4 different Power Clips (NA/JP, UK, EU, ANZ). By default the North American Power Clip comes installed on the Universal Power Adapter. Follow the steps below to switch the Power Clip.

- 1. Press the **PUSH Button**, located below the **Power Clip** on the **Universal Power** Adapter.
- 2. While holding the **PUSH Button**, slide the **Power Clip** upwards.
- 3. Locate the **Power Clip** that suits your application.
- 4. Slide the new **Power Clip** down into the **Universal Power Adapter** until you hear it Click.

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no quarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- · Increase the separation between the equipment and receiver.
- · Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

(1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Changes or modifications not expressly approved by StarTech.com could void the user's authority to operate the equipment.

Industry Canada Statement

This Class B digital apparatus complies with Canadian ICES-003.

Cet appareil numérique de la classe [B] est conforme à la norme NMB-003 du Canada.

CAN ICES-3 (B)/NMB-3(B)

This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two

(1) This device may not cause interference, and (2) This device must accept any interference, including interference that may cause undesired operation of the device.

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes:

(1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of thirdparty companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Warranty Information

This product is backed by a two-year warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

• If product has an exposed circuit board, do not touch the product under power.

Mesures de sécurité

• Si l'un des circuits imprimés du produit est visible, ne pas touchez le produit lorsqu'il est sous tension.

製品に露出した状態の回路基盤が含まれる場合、電源が入っている状態で製品に触らないでください。

Misure di sicurezza

• Se il prodotto ha un circuito stampato visibile, non toccare il prodotto quando è acceso.

Säkerhetsåtgärder

• Rör aldrig vid enheter med oskyddade kretskort när strömmen är påslagen.

StarTech.com Ltd. StarTech.com LLP 45 Artisans Cres London, Ontario N5V 5E9 Canada

2500 Creekside Parkwy Lockbourne, Ohio 43137

U.S.A.

StarTech.com Ltd. Unit B, Pinnacle 15 Gowerton Rd. Brackmills Northampton NN4 7BW United Kingdom

FR: startech.com/fr DE: startech.com/de ES: startech.com/es NL: startech.com/nl IT: startech.com/it JP: startech.com/jp