


4 Port Black SuperSpeed USB 3.0 Hub

Product Diagram (ST4300USB3)



	Port	Function
1	Power LED	<ul style="list-style-type: none"> Solid: Hub is receiving power.
2	USB-A Ports (4)	<ul style="list-style-type: none"> Used to connect USB devices to the Hub.



	Port	Function
3	Power Port	<ul style="list-style-type: none"> Used with the Power Adapter, to power the Hub.
4	USB-B Port (Host)	<ul style="list-style-type: none"> Used to connect the Host Computer to the Hub.

Requirements

For the latest requirements, please visit www.startech.com/ST4300USB3, www.startech.com/ST4300USB3EU, or www.startech.com/ST4300USB3GB

Installation

1. Connect the included power adapter to the USB hub. The power LED should light up solid. Supplying external power is optional, however to ensure each USB port is fully powered, connecting external power is recommended.
2. Connect the USB cable from the USB hub (type B port) to the host computer system.

NOTE: If connected to a USB 2.0 host port, the hub will only operate at USB 2.0 speeds.

3. The operating system should detect the hub immediately and automatically install it.
4. Once installation is complete, USB 1.x/2.0/3.0 devices should be able to be connected to the hub and recognized.

Specifications

Bus Interface	USB 3.0
Number of Ports	4
Connectors	<ul style="list-style-type: none"> USB-A x 4 USB-B x 1 DC Power x 1
LEDs	Power x 1
Maximum Data Transfer Rate	USB 3.0L 5 Gbps
Enclosure Material	Plastic
Power Adapter	5VDC, 2000mA, type M plug
Warning: Using an improper power adapter may cause damage to the HUB and any connected devices. Ensure that the correct adapter with a 5V output is used."	
Operating Temperature	0°C~55°C (32°F~131°F)
Storage Temperature	-20°C~85°C (-4°F~185°F)
Humidity	5%~95% RH
Dimensions	152.0mm x 59.6mm x 23.5mm
Weight	480g



FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment to an outlet on a different circuit than the receiver.
- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the device. If shielded interface cables are included with the product, or if additional components or accessories are designated for use with the installation, they must be used to ensure compliance with FCC regulations.

For the State of California

⚠ WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

ISED Statement / Déclaration d'ISDE

This Class B digital apparatus complies with Canadian ICES-003.

This device complies with ISED Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

Cet appareil numérique de la classe B est conforme à la norme NMB-003 du Canada.


Le présent appareil est conforme aux CNR d'ISDE Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes : (1) l'appareil ne doit pas produire de brouillage, et (2) l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

IC Radiation Exposure Statement

This equipment complies with IC RSS-102 radiation exposure limit set forth for an uncontrolled environment. This equipment should be installed and operated with minimum distance 0.5cm between the radiator and your body.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.



Points de collecte sur www.quefairedemesdechets.fr
Privilégiez la réparation ou le don de votre appareil !

Warranty Information

This product is backed by a two year warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability

In no event shall it be the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Safety Measures

- If product has an exposed circuit board, do not touch the product under power.

Mesures de sécurité

- Si l'un des circuits imprimés du produit est visible, ne pas toucher le produit lorsqu'il est sous tension.

安全対策

- 製品に露出した状態の回路基盤が含まれる場合、電源が入っている状態で製品に触らないでください。

Misure di sicurezza

- Se il prodotto ha un circuito stampato visibile, non toccare il prodotto quando è acceso.

Säkerhetsåtgärder

- Rör aldrig vid enheter med oskyddade kretskort när strömmen är påslagen.

**StarTech.com
Ltd.**

45 Artisans Cres
London, Ontario
N5V 5E9
Canada

StarTech.com LLP

4490 South Hamilton
Road
Groveport, Ohio
43125
U.S.A.

**StarTech.com
Ltd.**

Siriusdreef 17-27
Unit B, Pinnacle 15
Gowerton Rd,
Brackmills
Northampton
NN4 7BW
United Kingdom

StarTech.com Ltd.

2132 WT Hoofddorp
The Netherlands

FR: startech.com/fr
DE: startech.com/de
ES: startech.com/es
NL: startech.com/nl

IT: startech.com/it
JP: startech.com/jp