

8-Port Charging Station for USB Devices | 8x 2.4A

Product Diagram (ST8CU824)



Components	Function
1 Short-Circuit LEDs (8)	<ul style="list-style-type: none"> Solid Red: Indicates that the corresponding USB-A Port has shorted, and that the port has been deactivated, to protect the connected device. <ul style="list-style-type: none"> The port will remain deactivated until the Charging Station is power-cycled.
2 Power Button	<ul style="list-style-type: none"> Used to turn the Charging Hub On or Off.
3 DC IN 12V	<ul style="list-style-type: none"> Used to power the Charging Hub.
4 USB-A Ports (8)	<ul style="list-style-type: none"> Used to charge multiple Devices (max = 8). Voltage at the common collector (VCC) = 5V Ground (GND) = 5V D+ = 2.7V D- = 2.0V

To view manuals, FAQs, videos, drivers, downloads, technical drawings, and more, visit www.startech.com/support.

Requirements

For the latest requirements, please visit www.startech.com/ST8CU824

- Phillips Head Screwdriver (Optional)

Installation

Notes: The **Charging Hub** features a chipset that can detect the required charging mode of a device, and switch to the proper mode for full-speed charging (e.g. If an Apple device is connected, it will automatically charge to Apple charging mode specifications).

When charging multiple devices, the **Charging Hub** may become warm to the touch, this is normal and will not harm the connected **Device(s)**.

1. Connect the **Power Adapter** to an **AC Electrical Outlet** and the other end to the **DC IN 12V Port** on the **Charging Hub**.
2. Press the **Power Button** to turn the **Charging Hub** On.
3. Connect your **Device(s)** to the corresponding **USB-A Ports** on the **Charging Hub**.

Installing the Mounting Brackets (Optional)

Note: Before installing the **Mounting Bracket** to the mounting surface, contact a professional. Product mounting should be completed by a certified professional as per the local safety and building code guidelines.

1. Align the **Mounting Holes** on the **Mounting Bracket** with the four **Mounting Holes** on the back of the **Charging Hub**.
2. Insert the **Bracket Screws** (x4) through the **Mounting Bracket** and into the **Mounting Holes** on the back of the **Charging Hub**.
3. Tighten the **Mounting Screws** using a **Phillips Head Screwdriver**, be careful not to over-tighten.

Installing the Rubber Feet (Optional)

1. Remove the **Rubber Feet** from the **Adhesive Strip**.
2. Align each of the **Rubber Feet** on the back of the **Charging Hub**, close to each of the four corners.
3. Remove the adhesive backing and apply the **Rubber Feet** to the **Charging Hub**.

Note: Be careful not to cover the **Mounting Holes** when applying the **Rubber Feet**.

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

(1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Changes or modifications not expressly approved by StarTech.com could void the user's authority to operate the equipment.

Industry Canada Statement

This Class B digital apparatus complies with Canadian ICES-003.

Cet appareil numérique de la classe [B] est conforme à la norme NMB-003 du Canada.

CAN ICES-3 (B)/NMB-3(B)

This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions:

(1) This device may not cause interference, and (2) This device must accept any interference, including interference that may cause undesired operation of the device.

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes:

(1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

IC Radiation Exposure Statement

This equipment complies with IC RSS-102 radiation exposure limit set forth for an uncontrolled environment. This equipment should be installed and operated with minimum distance 0.5cm between the radiator and your body.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Warranty Information

This product is backed by a two-year warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Safety Measures

- If product has an exposed circuit board, do not touch the product under power.

Mesures de sécurité

- Si l'un des circuits imprimés du produit est visible, ne pas touchez le produit lorsqu'il est sous tension.

安全対策

- 製品に露出した状態の回路基盤が含まれる場合、電源が入っている状態で製品に触らないでください。

Misure di sicurezza

- Se il prodotto ha un circuito stampato visibile, non toccare il prodotto quando è acceso.

Säkerhetsåtgärder

- Rör aldrig vid enheter med oskyddade kretskort när strömmen är påslagen.

**StarTech.com
Ltd.**
45 Artisans Cres
London, Ontario
N5V 5E9
Canada

StarTech.com LLP
4490 South Hamilton
Road
Groveport, Ohio
43125
U.S.A.

**StarTech.com
Ltd.**
Siriusdreef 17-27
Unit B, Pinnacle 15
Gowerton Rd,
Brackmills
Northampton
NN4 7BW
United Kingdom

FR: startech.com/fr
DE: startech.com/de
ES: startech.com/es
NL: startech.com/nl
IT: startech.com/it
JP: startech.com/jp