

PINOUT:


P1		P2
1	— RED COAX COND	— 1
2	— GREEN COAX COND	— 2
3	— BLUE COAX COND	— 3
6	— RED COAX DRAIN	— 6
7	— GREEN COAX DRAIN	— 7
8	— BLUE COAX DRAIN	— 8

P1	COLOR	P2
4	BROWN	4
11	BROWN/WHITE	11
12	RED	12
15	RED/WHITE	15
5	ORANGE	5
5	ORANGE/WHITE	5
13	YELLOW	13
10	YELLOW/WHITE	10
14	BLACK	14
10	BLACK/WHITE	10
SHIELD		SHIELD

SPEC:

- CABLE UL2919 3COAX+5PAIR(28AWG) 100%AL DRAIN BRAID
JACKET BLACK IN COLOR OD:9.0MM
- HDD15PIN MALE BLACK COLOR PIN9 REMOVED SHELL NICKEL PLATED
- MOLDING SCREW 4-40UNC 4x49.5mm.
- 100%METAL SHELL OF HDD15PIN CONNECTORS
- MOLDING PVC BLACK IN COLOR.

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	MXTMMHQ18IN		
DESCRIPTION	18in Coax High Resolution VGA Monitor Cable - HD15 M/M		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 12/9/2020	