


PIN ASSIGNMENT

| P1    | WIRE TYPE | P2    | COLOR |
|-------|-----------|-------|-------|
| 1     |           | 1     | RED   |
| 2     |           | 2     | White |
| 3     |           | 3     | Green |
| 4     |           | 4     | BLACK |
| SHELL |           | SHELL | BRAID |



| SKU        | LENGTH    |
|------------|-----------|
| USB2HAB15T | 4575±55MM |
| USB2HAB10T | 3050±40MM |
| USB2HAB6T  | 1830±35MM |

| NO. | NAME      | MATERIAL DESCRIPTION   | Q'TY | UNITS | THIRD ANGLE PROJECTION   | StarTech.com        |                                    |                               |
|-----|-----------|--|------|-------|--|---------------------|------------------------------------|-------------------------------|
| 4   | OVER MOLD | PVC , COLOR:TRANSPARENT  | A/R  | KG    |  | <b>StarTech.com</b> |                                    |                               |
| 3   | CONNECTOR | USB B/M (SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.                  | 1    | SET   |  |                     |                                    |                               |
| 2   | CONNECTOR | USB A/M (SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.                  | 1    | SET   | <b>GENERAL NOTES</b><br>DIMENSIONS ARE IN MM - DO NOT SCALE<br>THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM | PRODUCT ID          | USB2HABxT                          |                               |
| 1   | CABLE     | USB 2.0 UL2725 28AWG*1P+24AWG*2C+AL/MY+D +B(16*4/0.12AL-M) OD:4.5mm TRANSPARENT PVC JACKET | A/R  | M     |  | DESCRIPTION         | Transparent USB 2.0 Cable - A to B |                               |
|     |           |  |      |       |  | <b>DO NOT SCALE</b> | <b>SHEET: 1 OF: 1</b>              | <b>UPLOAD DATE: 1/27/2022</b> |