


5 Channel Low Profile PCI Sound Card – 24 Bits

PCISOUND5LP



DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

Reorient or relocate the receiving antenna.

Increase the separation between the equipment and receiver.

Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

Introduction.....	1
Packaging Contents	1
System Requirements	1
Installation.....	1
Hardware Installation.....	2
Driver Installation	2
Physical Layout.....	3
Internal Header Connectors.....	3
Specifications.....	4
Technical Support	5
Warranty Information.....	5

Introduction

This 5 Channel PCI Sound Adapter Card is the ideal sound solution for low profile/small form factor PC computers, supporting full-duplex operation with 6 outbound streams and 2 simultaneous input streams. Offering everything you need to take your multimedia experience to the next level, the 5-channel sound card supports the latest Dolby Digital EX and DTS 5.1 Channel DVD soundtracks, and 96Khz/24bit audio playback.

The sound card includes Windows WDM supported drivers, which save both time and hassle, allowing you to add high quality audio in minutes. Equipped with a low profile bracket, the 5-channel Sound Card also includes a standard profile (full-height) mounting bracket and is PCI v2.2 compliant, so it can be installed in virtually any PCI-capable PC regardless of the size of the computer case - a cost-effective HTPC (Home Theater PC) solution! This high quality 5.1 Surround Sound card is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Packaging Contents

- 1 x PCISOUND5LP adapter card
- 1 x Full Profile Bracket
- 1 x Driver CD
- 1 x User Manual

System Requirements

- Available 5V compatible PCI slot
- Windows 2000/ XP(32/64-bit)/ 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)

Installation

It is recommended that you remove any previously installed sound card and drivers/software prior to installing the PCISOUND5LP sound card to avoid any conflicts. If previously installed drivers are not removed, the PCISOUND5LP sound card may not function properly. (Note: If your computer has on-board sound you may need to disable it on the motherboard. For more information please see your computer's documentation or contact your computer's manufacturer.)

Hardware Installation


1. Turn your computer off and any peripherals connected to the computer (ie. Printers, external hard drives, etc.). Unplug the power cable from the rear of the power supply on the back of the computer.
2. Remove the cover from the computer case.
3. Locate an open PCI slot and remove the metal cover plate on the rear of the computer case.
4. Insert the card into the open PCI slot and screw the bracket to the rear of the case.
NOTE: If the computer takes full profile expansion cards, the low profile bracket on the card will need to be changed with the included full profile bracket.
5. Place the cover back onto the computer.
6. Insert the power cable into the socket on the power supply and reconnect your other peripherals.

Driver Installation

Windows 2000/XP/Server 2003/Vista/7

1. After installing the card in the PC, power up the PC. You will be presented with the Found New Hardware prompt. Cancel this prompt.
2. Place the Driver CD into the CD-ROM drive. Click the Start button on the taskbar and click Run. Type "D:\SOUND\VT1723\setup.exe". (Assuming you have placed the CD in CD-ROM drive D:).
3. Follow any on-screen instructions to complete the software installation.
4. Restart your system.
5. Once you have rebooted the computer, the PCISOUND5LP sound card will be ready to use.

Physical Layout



1. **Line In** (blue) – Connect to the audio output of a stereo receiver, CD player, etc.
2. **Mic In** (pink) – Connect to the microphone (Mono).
3. **Front-Speaker** (green) – Connect to front speakers or earphones or audio-in of a stereo receiver.
4. **Rear-Speaker** (black) – Connect to the rear speakers when 4 or 6 channel speaker mode is enabled.
5. **Center/Sub-woofer** (orange) – Connect to the center speaker and sub-woofer when 6 channel speaker mode is enabled.

Internal Header Connectors

J10	Analog CD/IN (L-G-G-R)
J11	Analog CD/IN (G-R-G-L)
J12	Aux In

Specifications

Bus Interface	PCI v2.2 (5V)
Internal Connectors	1 x Aux-In header 2 x Analog CD/IN header
External Connectors	5 x 3.5mm Mini Jack (Line-In, Mic, Front Out, Rear Our, Center/Sub Out)
Chipset	VIA Tremor VT1723
Duplex Mode	Full Duplex: 6 output streams, 2 input streams
Maximum Sampling Rate	Playback: 96k/24-bit Recording: 48k/16-bit
Support Operating Systems	Windows 2000/ XP(32/64-bit)/ 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/ support and access our comprehensive selection of online tools, documentation, and downloads.

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

StarTech.com

Hard-to-find **made easy**®

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit **www.startech.com** for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.