


MARKING: USB 3.0 CABLE E139315-F5 AWM 2725 80° C 30V VW-1



Pin Assignment:

USB3.0 A/M		Wire	USB3.0 B/M		
Pin	Signal Name	Wire	Signal Name	Pin	Signal Name
1	VBUS	1	PWR	1	VBUS
2	D-	2	UTP_D-	2	D-
3	D+	3	UTP_D+	3	D+
4	GND	4	GND_PWRrt	4	GND
5	SSRX-	5	SDP1-	5	SSTX-
6	SSRX+	6	SDP1+	6	SSTX+
7	GND_Drain	7, 10	SDP1_Drain SDP2_Drain	7	GND_Drain
8	SSTX-	8	SDP2-	8	SSRX-
9	SSTX+	9	SDP2+	9	SSRX+
Shell	Shield	Braid	Shield	Shell	Shield

- NOTES:
- TESTING CONDITION:  
100% OPEN/SHORT/MISS WIRE TESTING  
INSULATION RESISTANCE: DC/250V, 10MΩ Min, 0.01S  
WITHSTAND VOLTAGE: AC/250V 5mA FOR 0.01S.  
CONDUCTOR RESISTANCE: 5Ω Max.
  - All Material Meet The RoHS Compliant.

⑥	TIE	BLACK PVC TIE	A/R
⑤	PVC	OVER MOLDING :PVC BLACK	A/R
④	PE	IN MOLDING : MG70 LDPE	A/R
③	USB3.0 B/M	USB 3.0 BM PLUG, Contact Plated G/F + SHELL Ni PLATED	1 SET
②	USB3.0 A/M	USB 3.0 AM PLUG, Contact Plated G/F + SHELL Ni PLATED	1 SET
①	CABLE	USB 3.0 CABLE 28AWG (7/0.127 TC)x3P+28AWG (7/0.127 TC)x2C OD:5.5MM BK012 PVC LP1111	A/R
No.	TITLE	DESCRIPTION	Q' TY

THIRD ANGLE PROJECTION

GENERAL NOTES  
DIMENSIONS ARE IN MM - DO NOT SCALE  
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

**StarTech.com**

PRODUCT ID	USB3SAB1MRA
DESCRIPTION	1m Black SuperSpeed USB 3.0 Cable - Right Angle A to B - M/M
DO NOT SCALE	SHEET: 1 OF: 1
UPLOAD DATE: 8/09/2021	