

USB3.0 AF(Nickel plated)
Connector Molding Thickness = 10±0.3

IDC 20F(PH=2.0mm)

NOTES:


OPEN/SHORT TEST:100% TEST.
INSULATION: MIN. 5MΩ.
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2

PIN ASSIGNMENT:

(P1)USB AF	1	5	6	7	8	9	4	2	3	64	
(P2)IDC 20F	1	TP		4	GND	TP		7	TP		4+13
(P3)USB AF	3	2	4	9	8	7	6	5	1	64	
(P2)IDC 20F	TP		13	TP		16	GND	TP		19	4+13

⑨	Copper foil	2PCS
⑧	L Metal bracket 120MM	1PCS
⑦	PE	10g
⑥	Blue 45P PVC	15g
⑤	Screw: #4-40(#4*10PM)	2PCS
④	Screw nut: #4-40(4.75*1.9mm)	2PCS
③	IDC 20F PH=2.0mm (Blue insulator)	1PCS
②	USB3.0 AF(Blue insulator,Nickel plated)	2PCS
①	UL2725 (28#*1P+D+AL+MY)*2C+28#*1P+24#*2C+AL+D+B(AM) OD=5.5MM Blue PVC Jacket	2PCS
No.	Description	Qty

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USB3SPATE		
DESCRIPTION	2 Port USB 3.0 A Female Slot Plate Adapter		
REV: 2	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 07/20/2020