

2-Port HDMI® Automatic Switch – 4K

VS221HD4KA

DE: Bedienungsanleitung - de.startech.com
 FR: Guide de l'utilisateur - fr.startech.com
 ES: Guía del usuario - es.startech.com
 IT: Guida per l'uso - it.startech.com
 NL: Gebruiksaanwijzing - nl.startech.com
 PT: Guia do usuário - pt.startech.com

Product overview

Front View

*actual product may vary from photos



1. Input selection button
2. Mode selection switch
3. IR sensor

Rear View



1. Power adapter port
2. RJ-11 serial jack
3. EDID copy button
4. HDMI output port
5. HDMI input ports (in1 & in2)
6. EDID setting switch

Packaging contents

- 1 x 2-port HDMI switch
- 1 x remote control
- 1 x universal power adapter (NA/EU/UK/AU)
- 1 x RJ11 cable
- 1 x RJ11 to DB-9 serial adapter
- 1 x mounting kit
- 1 x quick start guide

System requirements

- 2 x HDMI enabled Video Source Device w/ HDMI cable (i.e. Blu-ray player, computer, etc.)
- 1 x HDMI enabled Display Device w/ cable (i.e. Television, projector, etc.)

Operating system requirements are subject to change. For the latest requirements, please visit www.startech.com/VS221HD4KA.

Installation

Note: Ensure your HDMI enabled video source devices, and the HDMI enabled display are powered off before you begin installation.

1. Connect an HDMI cable (not included) from each of the HDMI output ports on your HDMI source devices, to the HDMI input port on the HDMI switch.
 - Notes:** Each port is numbered, please take note of which number is assigned to each HDMI source device.
2. Connect an HDMI cable (not included) from the output port on the HDMI Switch to your HDMI display device.
3. Power on your HDMI display, followed by each of your HDMI source devices.
4. Connect the included power adapter from an available power source to the power adapter port on the HDMI switch.
5. (Optional for serial control) Connect the included RJ11 cable to the RJ11 to DB-9 serial adapter. Then connect the D9 connector to a 9-pin serial port on your computer system.
6. Your HDMI switch is now ready for operation.

Operation

Automatic operation

The HDMI switch features automatic operation that allows the switch to automatically select the most recently activated or connected HDMI source device.

Simply connect a new device or turn on an already connected device to automatically switch video sources.

Priority operation

The HDMI switch features priority operation which will prioritize port 1 and port 2 respectfully. When you turn on the higher prioritized video source device (port-1), that video source will automatically be selected. Turning off the device will automatically switch back to the lower prioritized video source (port-2).

Manual operation

Manual mode enables you to switch between video sources with push button operation.

Manual operation with selection button

Press the input Selection button, on the front of the switch to toggle between each video source device.

The active port LED indicator will light as video sources are switched, indicating which port is selected.

Manual operation with remote control

Press 1 or 2 on the remote control to switch between HDMI ports in1 or in2 respectively.



2. Open your terminal software to communicate through the serial port that the switch is connected to, and use the on-screen commands displayed to operate and configure your switch.

Manual operation with serial control

1. Configure the settings on your serial port the below configuration: Baud

Rate: 38400 bps Data

Bits: 8

Parity: None

Stop Bits: 1

Flow Control: None

```

COM4_38400_None_8_1_Dumb Terminal
Booting ...
Booting ...
-----
Digital Switch Splitter 2 x 1 (MIC40 U) 4R2K
H/W version: B3 F/W version: 006-19
ESD Switch: Switch
RC ID: none
-----
*****
CR^n,a1,a2 - Copy EDD (Inventory) to all input ports
n: Method, a1:a2: Options
1, Copy from specified monitor a1
2, Copy from corresponding monitor (1 on 1)
3, Make 1024 x 768 EDD
4, Make 1280 x 800 EDD
5, Make 1280 x 1024 EDD
6, Make 1360 x 768 EDD
7, Make 1400 x 1050 EDD
8, Make 1440 x 900 EDD
9, Make 1600 x 900 EDD
10, Make 1600 x 1200 EDD
11, Make 1680 x 1050 EDD
12, Make 1920 x 1080 EDD
13, Make 1920 x 1200 EDD
14, Make 1920 x 1440 EDD
15, Make 2048 x 1132 EDD
16, Make 2560 x 1440 EDD
17, Make 2560 x 1600 EDD
18, Make 3840 x 2160 EDD
19, Make 4096 x 2160 EDD
More...

when n = 1:
a1: monitor index (1-2), a2: not required
when n = 2:
a1,a2: not required
when n = 3-15:
a1: video options
1, DVI 2, HDMI (2D) 3, HDMI (3D)
a2: audio options
1, LPCM 2 ch 8, DTS 5.1 ch
2, LPCM 5.1 ch 9, DTS HD 5.1 ch
3, LPCM 7.1 ch 10, DTS HD 7.1 ch
4, Dolby AC3 5.1 ch 11, MPEG4 AAC 5.1 ch
5, Dolby TrueHD 5.1 ch 12, 5.1 ch combination
6, Dolby TrueHD 7.1 ch 13, 7.1 ch combination
7, Dolby E-AC3 7.1 ch

AVI^n - Select input port n as the source of all output ports
AVO^n - Enable output port n
n: 1-max - output port, * - All ports
AVODI^n - Disable output port n
n: 1-max - output port, * - All ports
VS - View current settings
More...
PI - Product information
EQ^n - Set EQ level as n (1-8)
TFC^n - Set input VCO Gain level as n (1-8)
OVC^n - Set output VCO Gain level as n (1-8)
FACTORY - Reset as factory default setting
REBOOT - Reboot the device
RCID^n - Set Remote Control ID as n
n: 0 - Reset as null (Always enabled)
1-16 - Valid ID
BEEP^n - Beep on / off n: 0 - Off 1 - On
TTC^n - Set terminal interface m: 0 - Human 167 - Machine
LCK^n - Lock / Unlock device n: 0 - Unlock 167 - Lock
-----
State: OPEN TX:4 RX:2457
  
```

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Changes or modifications not expressly approved by StarTech.com could void the user's authority to operate the equipment.

Industry Canada Statement

This Class A digital apparatus complies with Canadian ICES-003.

Cet appareil numérique de la classe [A] est conforme à la norme NMB-003 du Canada.

CAN ICES-3 (A)/NMB-3(A)

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two year warranty.

StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.