

USB to Slimline SATA CD/DVD Optical Drive Enclosure

SLMSOPTB

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

Packaging Contents

- 1 x SLMSOPTB enclosure
- 1 x USB "Y" cable
- 1 x Package of screws
- 1 x Set of rubber feet
- 1 x installation Guide

System Requirements

- Slimline SATA CD/DVD optical drive
- USB enabled computer system with available port
- Microsoft® Windows® 2000/XP/Server 2003/Vista/Server 2008 R2/7 (32/64-bit), or Apple® Mac OS® X, or Linux®

Installation

1. Using a screw driver, remove the two small screws from the rear panel of the enclosure and remove the plastic bezel.
 2. The drive tray should now slide out from the front of the enclosure.
 3. Slide the slimline SATA optical drive into the drive tray from the front. Make sure the line up the slimline SATA connector on the drive to the connector at the rear of the tray.
 4. Once firmly seated, use the provided screws to secure the drive to the tray using the mounting points on the side of the drive/tray.
 5. Insert the assembled drive tray back into the enclosure housing.
 6. Replace the plastic rear bezel and fasten using the previously removed screws.
 7. Connect the provided USB cable from the enclosure to the host system. No driver installation is required.
- NOTE:** Only the Primary USB connector needs to be connected to the host system. If the optical drive requires more power than can be drawn from a single USB connector, then the Secondary connector may also be necessary.

Front View



Rear View



USB type mini-B connector

Specifications

Bus Interface	USB 2.0
ChipsetID	Sunplus SPDF303
Connectors	1 x USB type mini-B
Material	Aluminum (enclosure) Plastic (drive tray)
Power Adapter	None (USB powered)
Operating Temperature	0°C ~ 60°C (32°F ~ 140°F)
Storage Temperature	-20°C ~ 70°C (-4°F ~ 158°F)
Humidity	10 ~ 90% RH
Dimensions	151.0mm x 136.0mm x 20.0mm
Weight	270g
Compatible Operating Systems	Windows 2000/XP/Server 2003/Vista/ Server 2008 R2/7 (32/64-bit), Mac OS X, Linux

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names & Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.