

## DVI to DisplayPort Adapter with Audio


DVI2DPA

DE: Bedienungsanleitung - de.startech.com  
 FR: Guide de l'utilisateur - fr.startech.com  
 ES: Guía del usuario - es.startech.com  
 IT: Guida per l'uso - it.startech.com  
 NL: Gebruiksaanwijzing - nl.startech.com  
 PT: Guia do usuário - pt.startech.com

The DVI2DPA DVI to DisplayPort Adapter (with 2-Channel Audio) converts a DVI-D (Digital), Mini-DVI or HDMI source signal and accompanying audio, for use with a DisplayPort monitor.

Supporting resolutions up to 1920x1200, this USB-Powered device offers easy plug-and-play installation with both PC and Mac® platforms, ensuring seamless operation with your DisplayPort display to save the time and hassle of hardware upgrades.

A complete, out-of-the-package solution, this DVI DisplayPort adapter includes all cables necessary for connecting a DVI-D video source and accompanying audio (3.5mm stereo audio) to any DisplayPort monitor, and can also be used with Mini DVI or Mini HDMI sources using additional cables (sold separately).




\*actual product may vary from photos

## Packaging Contents

- 1 x DVI to DisplayPort Adapter
- 1 x DisplayPort Cable
- 1 x 1 x 3.5mm Audio Cable
- 1 x USB type mini-B to USB A Cable
- 1 x Instruction Manual

## System Requirements

- DVI-D enabled video source device (e.g. computer)
- Two adjacent USB ports on the video source device
- DisplayPort enabled display device (e.g. monitor)



## Installation

To ensure the best results, make sure all devices are powered off before beginning the installation.

1. Connect the DVI connector on the video converter directly to a DVI-D enabled video source (i.e. computer).
2. Using the included USB type mini-B to USB A cable, connect the video converter to a USB power source.
3. **OPTIONAL:** If using audio, connect a 3.5mm audio cable from the sound card to the video converter.
4. Connect a DisplayPort cable (sold separately) from the DisplayPort connector on the video converter, to the external display (i.e. monitor).
5. Power on the display.
6. Power on the video source.

## Specifications

<b>Video Signal</b>	DisplayPort 1.1a DVI-D (DDWG 1.0)
<b>External Connectors</b>	1 x DVI-D (25-pin) male 1 x DisplayPort female 1 x USB mini-B female 1 x 3.5mm Audio female
<b>LEDs</b>	1 x Power
<b>Maximum Video Resolution</b>	1920x1200
<b>Audio Support</b>	Yes (2-channel)
<b>EDID Support</b>	Yes
<b>Power Adapter</b>	USB powered
<b>Operating Temperature</b>	0°C ~ 70°C (32°F ~ 158°F)
<b>Storage Temperature</b>	-10°C ~ 80°C (14°F ~ 176°F)
<b>Humidity</b>	10% ~ 85% RH
<b>Integrated Cable Length</b>	61cm / 2ft
<b>Dimensions (LxWxH)</b>	76.2mm x 63.5mm x 6.6mm
<b>Weight</b>	200g

## FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

## Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

## Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit [www.startech.com/downloads](http://www.startech.com/downloads)

## Warranty Information

This product is backed by a one year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

## Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.