



Electrical Test:
 1.100%Test(Open ,short ,miss wire)
 2.Contact Resistance: 3 ohm max.
 3.Insulation Resistance: 10M ohm Min.300V DC/10ms.

6	HDMI AM~PVC Boarding Cap	2
5	Heat shrinkable casing	0.08
4	45P Black PVC	16
3	LDPE	4
2	HDMI M 19P~Insulator Black~Shell Gold plated~Pin Gold plated	2
1	(24AWG*2C+EAM+B 65%AL)*4P+[(28AWG*2C+EAM)+28AWG*4C+F+E+AL] OD:4.2*18MM~Black~Marking:High Speed...	7.65
NO	DESCRIPTION	Q'TY

THIRD ANGLE PROJECTION

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	HDMIMM25FL
DESCRIPTION	25 ft Flat High Speed HDMI Cable with Ethernet - Ultra HD 4k x 2k
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 3/25/2021