



**PIN ASSIGNMENT**

P1	WIRE TYPE	P2	WIRE COLOR
PIN1		PIN1	RED
PIN2		PIN2	WHITE
PIN3		PIN3	GREEN
PIN4		PIN5	BLACK
PIN5		PIN6	BLUE
PIN6		PIN7	YELLOW
PIN7		PIN8	DRAIN
PIN8		PIN9	PURPLE
PIN9		PIN10	ORANGE
SHELL		SHELL	DRAIN

**NOTES:**

- 1.OPEN/SHORT/INTERMITTENCE 100% TEST.
- 2.DIELECTRIC STRENGTH:300V AC 5mA/0.01S.
- 3.INSULATION RESISTANCE:300V DC/0.01S 10MΩ MIN.
- 4.CONDUCTIVE RESISTANCE:2Ω MAX.

5	IN MOLD	PE	/	KG
4	OVER MOLD	PVC 45P BLACK	/	KG
3	CONN	USB3.0 MICRO B/M SOLDER CONTACT:PIN G/F BLACK PLASTIC SHELL:NI-PLATED	1	SET
2	CONN	USB3.0 A/M SOLDER CONTACT:PIN G/F BLUE PLASTIC SHELL:NI-PLATED	1	SET
1	CABLE	UL20276,USB3.0 CABLE,(28#*1P+D+AL)*2+28#*1P +24#*2C,AeB(AL/Mg),BLACK,OD:5.5mm	A/R	PCS
No	PART	MATERIAL DESCRIPTION	Q'TY	UNITS

THIRD ANGLE PROJECTION

GENERAL NOTES		PRODUCT ID	USB3SAUB3BK	
DIMENSIONS ARE IN MM - DO NOT SCALE		DESCRIPTION	3 ft Black SuperSpeed USB 3.0 Cable A to Micro B - M/M	
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM		DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 8/23/2021