


United Kingdom Power Module BOX4MODULE | BEZ4MOD


Product Design

Actual product may vary from photos

Front View



Rear View



Package Contents

- Power Module x 1
- Power Cord x 1
- Installation Kit x 1
 - Mounting Bracket x 1
 - Mounting Bracket Screws (M5 x 20 mm) x 4
 - Module Screws (#6-32 x 3/16) x 8
- User Manual x 1

SKU: BNDBXHDBTPUK, BNDBXDOCKPUK, or BNDBXAVHDPUK

- Conference Table Box x 1
- Installation Kit x 1
 - Die Cut Outline x 1
 - Wing Nut Bracket

Requirements

For the latest requirements, please visit www.startech.com/MOD4POWERUK.

Installation

See the Installation section in the **Modular Table Box (BOX4MODULE)** or **Single-Module Table Box (BEZ4MOD) User Manual** for instructions on how to install a module into a table surface.

(Optional) Mounting

Note: StarTech.com is not responsible for any damages related to the installation of this product.

Installation Requirements:

- Mounting Bracket x 1
- Bracket Screws (M5 x 20 mm) x 4
- Module Screws (#6-32 x 3/16) x 8
- Writing Utensil x 1
- Phillips Head Screwdriver x 1

Note: Before mounting the **Module**, take into consideration the mounting orientation of the **Module**. This will affect the orientation of the ports (top and bottom).

1. Align the **Mounting Bracket** with the four **Mounting Holes** on the **Module**.

Note: The **Module** has four **Mounting Holes** on each side, which gives you two different mounting options.

2. Insert the **Bracket Screws** (x4) through the **Mounting Bracket** and into the **Mounting Holes**.
3. Tighten the **Mounting Screws** using a **Phillips Head Screwdriver**, be careful not to overtighten.
4. Before installing the **Mounting Bracket**, measure and position the **Mounting Bracket** in the desired location. The **Module** can be mounted on a vertical or horizontal surface.

Note: Depending on the surface you are using to install the product, you may need to drill pilot holes prior to installing the screws into the surface.

5. Mark the location of the **Mounting Holes** using a **Writing Utensil**. These marks can be used as a guide to indicate where the **Mounting Screws** will be installed in the surface.
6. Install the **Bracket Screws** (x4) through the **Mounting Bracket** and into the mounting surface, using a **Phillips Head Screwdriver**. Be careful not to overtighten.

Warning: To prevent the **Mounting Screws** from penetrating the opposite side of the installation surface, be conscious of the size of the **Mounting Screw** compared to the depth of the surface.

Powering the Module

1. Connect the **Power Cord** to the **C14 Power Receptacle**, on the bottom of the **Power Module**.
2. Connect the other end of the **Power Cord** to an **AC Electrical Outlet**.

Connecting a Device to the Module

USB-A Port

The **USB-A Port** will charge up to two **USB Devices** (e.g. Cell Phone, Laptop, Tablet, etc.).

Note: The **USB-A Ports** support Smart Charging (Smart IC). Smart Charging supports a wide variety of charging protocols (e.g. Battery Charging 1.2, Apple, Samsung™, etc.).

Connecting a Device to the USB-A Port

1. Connect a **USB-A Cable** to the **USB-A Port** on the top on the **Module**.
2. Connect the other end of the **USB-A Cable** to a **USB Port** on your device.

Note: The type of **USB Port** on the connected device will vary depending on the device.

AC Electrical Outlet

The **AC Electrical Outlet** will charge either one or two connected devices using an **AC Power Adapter**.

Note: The number of **AC Electrical Outlets** varies depending on the region specific Power Module (e.g. UK/EU = 1 x AC Electrical Outlet and NA = 2 x AC Electrical Outlets).

1. Connect an **AC Power Adapter** into a **Power Adapter Port** or **USB Port** (depending on port configuration) on the device you want to charge.
2. Connect the other end of the **AC Power Adapter** into the **AC Electrical Outlet** on the **Power Module**.

Safety Measures

- If product has an exposed circuit board, do not touch the product under power.
- Wiring terminations should not be made with the product and/or electric lines under power.
- Product installation and/or mounting should be completed by a certified professional as per the local safety and building code guidelines.
- Cables (including power and charging cables) should be placed and routed to avoid creating electric, tripping or safety hazards.

Mesures de sécurité

- Si l'un des circuits imprimés du produit est visible, ne pas touchez le produit lorsqu'il est sous tension.
- Les terminaisons de câblage ne doivent pas être effectuées lorsque le produit et/ou les câbles électriques sont sous tension.
- L'installation et/ou le montage du produit doit être réalisé par un professionnel certifié et dans le respect des normes locales et du code de construction local.
- Les câbles (y compris les câbles d'alimentation et de chargement) doivent être placés et acheminés de façon à éviter tout risque électrique, de chute ou de sécurité

安全対策

- 製品に露出した状態の回路基板が含まれる場合、電源が入っている状態で製品に触らないでください。
- 電源が入っている状態の製品または電線の終端処理を行わないでください。
- 製品の設置やマウントは、使用地域の安全ガイドラインおよび建築基準に従い、有資格の専門業者が行うようにしてください。
- ケーブル（電源ケーブルと充電ケーブルを含む）は、適切な配置と引き回しを行い、電気障害やつまつきの危険性など、安全上のリスクを回避するようにしてください。

Misure di sicurezza

- Se il prodotto ha un circuito stampato visibile, non toccare il prodotto quando è acceso.
- I terminali dei fili elettrici non devono essere realizzate con il prodotto e/o le linee elettriche sotto tensione.
- L'installazione e/o il montaggio dei prodotti devono essere eseguiti da un tecnico professionale certificato che conosca le linee guida locali sulle norme edilizie e sulla sicurezza.
- I cavi (inclusi i cavi di alimentazione e di ricarica) devono essere posizionati e stesi in modo da evitare pericoli di inciampo, rischi di scosse elettriche o pericoli per la sicurezza.

Säkerhetsåtgärder

- Rör aldrig vid enheter med oskyddade kretskort när strömmen är påslagen.
- Montering av kabelavslutningar får inte göras när produkten och/eller elledningarna är strömförda.
- Installation och/eller montering får endast göras av behöriga yrkespersoner och enligt gällande lokala förordningar för säkerhet och byggnormer.
- Kablar (inklusive elkablar och laddningskablar) ska dras och placeras på så sätt att risk för snubblingsolyckor och andra olyckor kan undvikas.

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and

on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help

LED Indicator

Power LED:

Solid LED (White)

- Indicates that the **Power Module** is active (the **Power Cord** is correctly connected to an **AC Electrical Outlet**).

LED Off

- Indicates that the **Power Cord** is not correctly connected to an **AC Electrical Outlet** or the **Power Module** is not receiving power from the **AC Electrical Outlet**.

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

(1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Changes or modifications not expressly approved by StarTech.com could void the user's authority to operate the equipment.

For the State of California

▲ **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Industry Canada Statement

This Class B digital apparatus complies with Canadian ICES-003.

Cet appareil numérique de la classe [B] est conforme à la norme NMB-003 du Canada.

CAN ICES-3 (B)/NMB-3(B)

This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions:

(1) This device may not cause interference, and (2) This device must accept any interference, including interference that may cause undesired operation of the device.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com.

Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/ support and access our comprehensive selection of online tools, documentation, and downloads. For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a one-year warranty. StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

StarTech.com Ltd.

45 Artisans Cres.
London, Ontario
N5V 5E9
Canada

StarTech.com LLP

2500 Creekside Pkwy.
Lockbourne, Ohio
43137
U.S.A.

StarTech.com Ltd.

Unit B, Pinnacle 15
Gowerton Rd., Brackmills
Northampton
NN4 7BW
United Kingdom

FR: fr.startech.com

DE: de.startech.com

ES: es.startech.com

IT: it.startech.com

JP: jp.startech.com

NL: nl.startech.com