StarTechcom

Hard-to-find made easy®

eSATA USB 2.0 to SATA Dual Hard Drive Docking Station

SATADOCK22UE SATDOCK2UEGB SATDOCK2UEEU



*actual product may vary from photos

DE: Bedienungsanleitung - de.startech.com FR: Guide de l'utilisateur - fr.startech.com ES: Guía del usuario - es.startech.com IT: Guida per l'uso - it.startech.com NL: Gebruiksaanwijzing - nl.startech.com PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to readio reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.



Table of Contents

Introduction	1
Features	1
Package Contents	1
SATADOCK22UE	2
Disk Installation	3
SATA Drive Removal	3
Preparing the Hard Drives for Use	4
Specifications	7
Technical Support	9
Warranty Information	9



Introduction

Thank you for purchasing a StarTech.com SATA HD Docking station. This unit allows you to install and access SATA drives quickly, and without the need for an enclosure. Simply plug the hard drive into the upright dock and connect it to a PC or notebook. The StarTech.com SATA HD Docking Station is a perfect solution for data recovery, drive imaging, and testing centers, or any environment requiring fast access to uninstalled/ archived drives.

Features

- Hot Swap Compatible
- · Plug and Play support for most operating systems
- Supports both SATA 2.5" and SATA 3.5" hard drives without and adapters


Package Contents

SATADOCK22UE

- 2x eSATA Cable
- Manual
- Power Adapter
- SATA Hard Drive Docking Station
- USB Cable



SATADOCK22UE








Disk Installation

- 1. Connect the Dock to an available power outlet, using the provided power adapter.
- 2. Connect the Dock to the (powered) Host Computer, using the provided USB/eSATA cables.
- 3. Insert the 2.5" or 3.5" SATA/SATA II drive(s) you wish to install, such that the SATA power and data connectors at the back of the drive are properly aligned with the corresponding connectors inside the Dock.



4. Press the Power Button on the rear panel of the Dock

Once the drive has been inserted, the operating system will detect that it has been connected and automatically update the drivers for proper operation.

SATA Drive Removal

If you are using the SATADOCK22UE, the drives can be removed using the eject button that corresponds with the drive you wish to remove.

When removing the installed drive from the Dock, please ensure that you have followed the appropriate steps (dependant on the operating system) to disconnect removable storage. In Windows for example, click on the Safe Remove icon located in the taskbar. Select the drive from the menu provided, then click Stop. Select the device to disconnect, and click OK.



Preparing the Hard Drives for Use

 With the hard drives inserted and the SATA DOCK powered on, right click on the My Computer icon and select Manage. In the left pane of the Computer Management window, click Disk Management.

E Computer Hanagement							1	
	icio							_@×
⇔ → 🕲 🖼 😫								
Computer Management (Local)		Type File System		Capacky			Fault Tolerance	
System Tools System Tools See Event Viewer See Shared Polders Onvice Honoger See Shared Storage	⊕(C) Partition	Dank MTPS	Healthy (System)	137.00 GB	133.33 68	97 %	No	0%
Cisk Defragnenter	<							>
(i) (() Services and Applications	CPDesk 0 Desk 137.00 GB Online	(C) 137.00 (8 MPS Healty (System)						
	GROME 1 Danic 1493.05 GD Online	149.05 Q8 Unallocated						
< > >	Unallocated	Primary partition						

 In the bottom right pane of the Computer Management window, you should see your drives listed as unallocated. Click on the unallocated drive and select New Partition. The New Partition Wizard will launch.

Sampater Management								1	. 🗆 🛛
🛃 File Action Were Mindow H									<u>.</u>
Computer Management (Loca)	Volume Layout	Type F	We System	Salue	Capacity	Free Space	% Free	Fault Tolerance	Overhead
Constant Soli Constant Soli Constant Soli Constant Solid Constant So	C) Partitor	n Bank P	साम्ड	Healthy (System)	137.40 GB	133.33 68	97 N	No	0%
B Services and Applications	Colore Colore		GB NTFS (System)						10 I
	Bate 1 Desit 143.05 GB Celine	143.05 Unalis:	ated	New Partition					∕
\$\$	 Unalocated 	Printagy p	wince	Help					

3. When the New Partition Wizard appears, click Next to continue





4. Select the partition type you wish to create by clicking on Primary or Extended, as appropriate. When you have made your selection, click Next to continue.



Specify the size of the partition you wish to create. You must select a partition size that is between the maximum and minimum sizes (typically the maximum disk space available). Once you have done so, click Next to continue.

Specify Partition Size Choose a partition size that is between the	e maximum and minimum sizes.
Maxium disk space in megabytes (MB): Minimum disk space in MB: <u>P</u> antion size in MB:	153625 8 1888888 🔹
	(Back Nett) Cancel

Select Format this partition with the following settings. Using the drop down buttons, select the file system, allocation unit size, and volume label you wish to use. Select Perform a Quick Format and click Next to continue.

To store data on this partition, ye	ou must format it first.		É
Choose whether you want to for	nat this partition, and if	so, what settings you w	vent to use.
O Do not format this pathlion			
 Format this partition with the 	ne following settings:		
Elle system	NTFS	~	
Allocation unit size:	Default	~	
⊻olume labet	New Volume		
Perform a quick for	nat		
	er compression		
Enable file and folde			



7. A notification window will appear indicating that you have successfully completed the New Partition Wizard. Click Finish to commence the formatting of the drive.



 The status of the drive, as shown in the Computer Management window, will be updated to reflect the selections you have made. Please wait while the drive is being formatted.

R Ne Action View Window H	Nelp							_ (#) ×
• - • • • • • • •	8 18							
Computer Hanagement (Joca) Sostem Tools Sostem Tools Sostem Tools Sostem Tools Sostem Tools Sostem Tools Sostem Hanager Sostem Tools S	Visune Layout ICO Paritice (E) Paritice		Status Healthy (System) Formatting	Capacity 137.00 68 149.05 68	Pres Space 133.33 GB 149.05 GB	% Pree 97 % 100 %	Pault Talerance No No	Overhead 0% 0%
Disk Defragmenter Disk Management	<							>
Borvices and Applications	EPback 0 Basic 127.00 GB Croine	(C:) 137.00 GB NTFS Healthy (System)						
	SPDark 1 Dark	(0)						
	149.05 GB Online	tiological Pormatting						1114 🕁

9. Once the drive has been successfully partitioned and formatted, it will display as Healthy.

Scomputer Nanogament										🛛
🛃 Ble Action Year Window E										
◆ → 🗈 🖻 🕄 🖆 🖬										
Sonputer Management (Local)				File System		Capacity	Free Space			
🗟 🍒 System Tools		Partition			Healthy (System)		133.33 68	97 %	No	0%
Control Verver		Fartition	Basic	MIPS	Healty	149.05 GB	143.96 (8	99%	No	0%
Control Contro Control Control Control Control Control Control Control Control Co	S Cont		00	,		12				
	137.00 Online	-	Heal	00 Q8 NTPS Try (System)						
	Besit 149.05 Online		Ncm 143 Heal	Volume (E 05 GB NTPS Try	2					
< >	Prince	ey patition								



10. To access your newly partitioned drive(s), open My Computer. Your drive(s) should be displayed below the heading Hard Disk Drives.

9e Edk Yew Fyrankes Sook	94		
0 · O · 1 P	Search 🜔 Publieri 🛄 •		
danse Mr Conputer			× 23 4
System Lasks A Wraw poten information M Add or remove programs P Change a setting M	Files Stored on This Computer	started's Documents	
Other Maces Point National Places Point National Places Point National Documents Point Shared Documents Point Shared Documents	Devices with Removable Storage	terr values (C)	
Details 8. My Caregodier System Folder	2% Peppy (A.)	CHC AMM Carry (Cr)	

Specifications

SKU	
Specification	SATADOCK22UE
Internal	2x SATA Power
Connectors	15-pin Female
	2x SATA Data
	7-Pin Female
External	1x USB B Female
Connectors	2x eSATA Plug Female
	1x DC Power Adapter
Drive Compatibility	2.5/3.5" SATA Hard Drives
OS Support	Windows 2000/2003/XP/Vista/7 x64/x86, Mac OS 10.0 and up, Linux
Power Adapter	12V/5V 3.0A



Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.



StarTechcom

Hard-to-find made easy®

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.